






客户图



Note:

- Material (材料):
Housing: PA46+30%GF (胶芯: PA46)
Barrel: Brass C3604 (针管: 黄铜 C3604)
Plunger: Brass C3604 (针头: 黄铜 C3604)
Spring: SUS304 (弹簧: SUS304)
- Plating (电镀):
Barrel: 5u' Au over 50~80u' Ni (针管: 镀金5u', 镍底50~80u'.)
Plunger: 5u' Au over 50~80u' Ni (针头: 镀金5u', 镍底50~80u'.)
Spring: No flash (弹簧: 不电镀)
- Electrical (电气特性):
Rated Current & Voltage: DC 12V; 1A (额定电压&电流: 直流12V, 1A)
Contact Resistance: 50 mohm Max. at working height.
接触电阻: 最大50毫欧 (在工作高度状态下)
Insulation Resistance: 1,000M Ω minimum. (绝缘电阻: 1,000M Ω 以上)
Dielectric Withstand Voltage: 500VAC/minute. (抗电压: 500VAC/minute)
- Mechanical (机械性能):
Force: 20g $\pm$ 5g at working height. (20g $\pm$ 5g 在工作高度).
Durability: 10,000 cycles (min) (寿命: 10000次)
- Work Temperature (工作环境):
Withstanding Higt Temperature: 280 $^{\circ}$ C
Operational Temperature: -40 $^{\circ}$ C ~ +85 $^{\circ}$ C

深圳市鑫扬泽电子有限公司

HTTP://WWW.XYZPOGOPIN.COM

TEL: 0755-28773277 FAX: 0755-28891353



SCALE:	N/A	UNIT	mm
SHEET:	1 of 1	PROJECTION	
DATE:	2023.8.10	VER.	D.0

THE UNMARKED TOLERANCE ARE AS BELOW :

LENGTH		ANGLE	
X.XX	± 0.05 mm	X.XX	$\pm 0.50^{\circ}$
X.X	± 0.10 mm	X.X	$\pm 1.00^{\circ}$
X.	± 0.20 mm	X.	$\pm 2.00^{\circ}$

DESIGNED BY:		DWG. NO.	YZP0819-20125-02025-02
CHECKED BY:		TITLE:	Pogo pin 连接器
APPROVED BY:			