





REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2025.11.03	
/	N/A		/	/	/



- Specifications()
- 1.Voltage rating():1500V DC
 - 2.Current rating():300A
 - 3.Withstanding voltage():4000V AC 1Min, 2mA MAX
 - 4.Insulation resistance():200MΩ MIN at DC500V
 - 5.Protection level():IP67
 - 6.Recommended screw torque():
 - 7.Temperature range():-40 ~+125

KHB-003 V-50 C8-OR

10.60~11.40mm) OR:Orange

12.50~13.50mm)

14.40~15.60mm) C8:M8

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	VIEW:	MODEL TYPE:
CHECKED	UNIT: mm/in	PART NO.: KHB-003V-50C8-OR
APPROVED	SIZE: A4	DWG NO.: