






REVISES					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2025.11.03	
/	N/A		/	/	/




2PCS




2PCS




2PCS



2PCS



PCB LAYOUT



KCT-123-04 0

2A=2.5mm²(:5.70±0.30)
04=4.0mm²(:5.70±0.30)

- Specifications()
- 1.Voltage rating():1000V DC
 - 2.Current rating():250A
 - 3.Withstanding voltage():3000V AC 1Min, 5mA MAX
 - 4.Insulation resistance():≥500MΩ at DC1000V
 - 5.Protection level():IP67
 - 6.Recommended screw torque():M4 1.5~2.0N.m
 - 7.Temperature range():-40 ~+125

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN		VIEW:	MODEL TYPE: 2
CHECKED		UNIT: mm/in	PART NO.: KCT-123-040
APPROVED		SIZE: A4	DWG NO.: