



1

2

3

4

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2026.03.30	
/	N/A		/	/	/



Specifications()

1.Voltage rating():750V DC

2.Current rating(): 400A;
200A

3.Withstanding voltage():3500V AC




4.Insulation resistance():100MΩ MIN at DC1000V

5.Protection level():IP67

6.Mating cycles 500 cycles Min

7.Recommended screw torque():
M5 0.5N.m M8 12.0N.m

8.Temperature range(): -40 ~+130



KMSD-211 F-200A-B8

200

B8:M8

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN		VIEW:	MODEL TYPE:
CHECKED		UNIT: mm/in	PART NO.: KMSD-211F-200A-B8
APPROVED		SIZE: A4	DWG NO.:

1

2

3

4