

5-Ampere, 50-1000 Voltage Surface Mount Fast Recovery Silicon Rectifiers

■ Features


- Glass passivated chip
- Low reverse leakage current
- Fast reverse recovery time
- High surge current capability
- The plastic case material has UL flammability classification rating 94V-0

■ Mechanical Data

- Package: SMB
- Polarity: As marked
- Lead free complies with the EU ROHS directive
- Terminals: Tin plated leads, solderable per Mil-STD-750 Method 2026



Key Parameters		
Parameter	Value	Unit
I_F	5	A
V_{RRM}	50~1000	V
I_{FSM}	125	A
Package	SMB	



■ Typical applications

- For use in general purpose rectification of power supplies, inverters, converters and freewheeling diodes for consumer, and telecommunication.

■ Maximum Ratings @ $T_a = 25^\circ\text{C}$ unless otherwise noted

PARAMETER		SYMBOL	RS5AB	RS5BB	RS5DB	RS5GB	RS5JB	RS5KB	RS5MB	UNIT
Maximum recurrent peak reverse voltage		V _{RRM}	50	100	200	400	600	800	1000	V
Maximum RMS voltage		V _{RSM}	35	70	140	280	420	560	700	V
Maximum DC Blocking Voltage		V _{DC}	50	100	200	400	600	800	1000	V
Maximum average forward rectified current at T _L =100°C		I _{FM}	5							A
Maximum instantaneous forward voltage @I _F =I _{FM}		V _F	1.3							V
Forward Surge Current (Non-repetitive) @ 60Hz Half-sine wave,1 cycle, T _j =25°C		I _{FSM}	125							A
Maximum Reverse recovery time @I _F =0.5A ,I _R =1A ,I _{rr} =0.25A		T _{RR}	150				250	500		nS
Junction temperature range		T _j	-55~+150							°C
Storage temperature range		T _{STG}	-55~+150							°C
Maximum DC reverse current at rated DC blocking voltage	T _j =25°C	I _R	5							μA
	T _j =100°C		200							μA

■Characteristic Curve




FIG1. Forward Current Derating Curve




FIG2. Maximum Non-Repetitive Peak Forward Surge Current




FIG3. Typical Forward Voltage Characteristics




FIG4. Typical Reverse Characteristics

■ Package Outline Dimensions (SMB/DO-214AA)

Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A	1.85	2.21	0.073	0.087
B	4.25	4.85	0.167	0.191
C	3.30	3.94	0.130	0.155
D	2.15	2.65	0.085	0.104
E	0.75	1.52	0.030	0.060
F	-	0.203	-	0.08
G	5.08	5.59	0.200	0.220
H	0.15	0.31	0.006	0.012

■ Suggested Pad Layout

Symbol	Reference Dimensions	
	Millimeters	Inches
A	2.30	0.091
B	2.10	0.085
C	2.70	0.106

■ Ordering Information

Package	Reel Size	Reel(pcs)	Identification
SMB	13"	3000	TQS

Notice

XILONG reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to any product herein. xilong does not assume any liability arising out of the application or use of any product described herein.