


# 客户图



## Note:

- Material(材料):  
Barrel: Brass C3604 (针管: 黄铜 C3604)  
Plunger: Brass C3604 (针头: 黄铜 C3604)  
Spring: SUS304 (弹簧: SUS304)
- Plating(电镀):  
Barrel: 3u' Au over Cu:50-100u", Ni60-120u"  
(针管: 镀金3u', 铜底50~100u", 镍底60~120u'.)  
Plunger: 3u' Au over Cu:50-100u", Ni60-120u"  
(针头: 镀金3u', 铜底50~100u", 镍底60~120u'.)  
Spring: gold plated (弹簧: 镀金)
- Electrical(电气特性):  
Rated Current & Voltage: DC 12V;3A  
(额定电压&电流: 直流12V,3A)  
Contact Resistance: 50 mohm Max. at working height.  
接触电阻: 最大50毫欧 (在工作高度状态下)
- Mechanical(机械性能):  
Force: 60g±20% at working height.  
(60g±20% 在工作高度)。)  
Full stroke: 2.50mm (全行程: 2.50mm)  
Durability: 10.000 cycles(min) (寿命: 10000次)
- WorkTemperture(工作环境):  
Withstanding Higt Temperature: 280℃  
Operational Temperature: -20℃~ +70℃

深圳市鑫探技术有限公司

HTTP://WWW.XYZPOGOPIN.COM

TEL:0755-28773277 FAX:0755-28891353



|        |           |            |     |
|--------|-----------|------------|-----|
| SCALE: | N/A       | UNIT       | mm  |
| SHEET: | 1 of 1    | PROJECTION |     |
| DATE:  | 2024.4.16 | VER.       | D.0 |

| THE UNMARKED TOLERANCE ARE AS BELOW : |         |       |        |
|---------------------------------------|---------|-------|--------|
| LENGTH                                |         | ANGLE |        |
| X.XX                                  | ±0.05mm | X.XX  | ±0.50° |
| X.X                                   | ±0.10mm | X.X   | ±1.00° |
| X.                                    | ±0.20mm | X.    | ±2.00° |

|              |  |          |                  |
|--------------|--|----------|------------------|
| DESIGNED BY: |  | DWG. NO. | YZP0669-40165-03 |
| CHECKED BY:  |  | TITLE:   | Pogo pin连接器      |
| APPROVED BY: |  |          |                  |