


客户图



Note:

1: Material (材料):

Barrel: Brass C6801 (针管: 无铅铜 C6801)

Plunger: Brass C6801 (针头: 无铅铜 C6801)

Spring: SUS304 (弹簧: SUS304)

2: Plating (电镀):

Barrel: 5u' Au over 200u' Cu over 200u' Ni (针管: 镀金5u', 铜底200u', 镍底200u').

Plunger: 5u' Au over 200u' Cu over 200u' Ni (针头: 镀金5u', 铜底200u', 镍底200u').

Spring: No plated (弹簧: 不镀金)

3: Electrical (电气特性):

Rated Current & Voltage: DC 12V;2A (额定电压&电流: 直流12V,2A)

Contact Resistance: 50 mohm Max. at working height.

接触电阻: 最大50毫欧 (在工作高度状态下)

4: Mechanical (机械性能):

Force: 200g $\pm$ 20% at working height. (200g $\pm$ 20%在工作高度)。

Durability: 10,000 cycles (min) (寿命: 10000次)

5: WorkTemperture (工作环境):

Withstanding Higt Temperature: 280℃

Operational Temperature: -20℃~ +70℃

深圳市鑫扬泽电子有限公司

HTTP://WWW.XYZPOGOPIN.COM

TEL:0755-28773277 FAX:0755-28891353



SCALE:	N/A	UNIT	mm
SHEET:	1 of 1	PROJECTION	
DATE:	2014.04.21	VER.	D.0

THE UNMARKED TOLERANCE ARE AS BELOW :			
LENGTH		ANGLE	
X.XX	$\pm 0.05\text{mm}$	X.XX	$\pm 0.50^\circ$
X.X	$\pm 0.10\text{mm}$	X.X	$\pm 1.00^\circ$
X.	$\pm 0.20\text{mm}$	X.	$\pm 2.00^\circ$

DESIGNED BY:		DWG. NO.	YZP0794-35101-02
CHECKED BY:		TITLE:	POGO pin
APPROVED BY:			