

Features

- Effectively lower down T_j and R_{th} , high anti-EMI ability
- High speed switching with low capacitances
- High blocking voltage with low $R_{DS(on)}$
- Easy to drive and parallel
- RoHS compliant

Benefits

- Increased power density
- Higher operating frequency
- Reduced heat sink requirements
- Higher efficiency
- EMI reduction


Applications

- Power factor correction modules
- Switch mode power supplies
- Power inverters
- High voltage converters

Parameter	Rating	Units
V_{DS}	800	V
$I_D @ 25^\circ\text{C}$	15	A
$R_{DS(on)}$	260	mΩ



TO-220F (Full Pack)



Part Number	Package	Marking
GC3M026065F	TO-220F	GC3M026065

Maximum Ratings ($T_j = 25^\circ\text{C}$ unless otherwise specified)

Symbol	Parameter	Test conditions	Value	Unit
V_{DS}	Drain-Source Voltage	$V_{GS} = 0\text{ V}, I_D = 100\text{ uA}$	800	V
I_D	Continuous Drain Current	$T_c = 25^\circ\text{C} \quad T_c = 100^\circ\text{C}$	15 12	A
I_{DM}	Peak Drain Current	Pulse width tp limited by T_{jmax}	39	A
$V_{GS\text{ max}}$	Gate-Source Voltage		-5/ 26	V
$V_{GS\text{ op}}$	Recommend Gate-Source Voltage		0/ 18	V
P_{tot}	Power Dissipation	$T_c = 25^\circ\text{C} \quad T_c = 100^\circ\text{C}$	52 25	W
T_j	Operating Junction Temperature		-55~175	$^\circ\text{C}$
T_{stg}	Storage Temperature		-55~175	$^\circ\text{C}$

Electrical Characteristics ($T_c = 25^\circ\text{C}$ unless otherwise specified)

Symbol	Parameter	Min.	Typ.	Max.	Unit	Test Conditions	Note
$V_{(BR)DSS}$	Drain-Source Breakdown Voltage	800			V	$V_{GS} = 0\text{ V}, I_D = 1\text{ mA}$	
I_{DSS}	Zero Gate Voltage Drain Current		1	15	μA	$V_{GS} = 0\text{ V}, V_{DS} = 850\text{ V}$	
I_{GSS}	Gate-Source Leakage Current			50	nA	$V_{DS} = 0\text{ V}, V_{GS} = 18\text{ V}$	
$V_{GS(th)}$	Gate Threshold Voltage		3.5	4.0	V	$V_{GS} = V_{DS}, I_{DS} = 1\text{ mA}, T_J = 25^\circ\text{C}$	Fig. 14
			2.8			$V_{GS} = V_{DS}, I_{DS} = 1\text{ mA}, T_J = 175^\circ\text{C}$	
$R_{DS(on)}$	Static Drain-Source On-Resistance		260 180	300 220	$\text{m}\Omega$	$V_{GS} = 15\text{ V}, I_D = 4.5\text{ A}, T_J = 25^\circ\text{C}$ $V_{GS} = 18\text{ V}, I_D = 4.5\text{ A}, T_J = 25^\circ\text{C}$	Fig. 15
			295 205			$V_{GS} = 15\text{ V}, I_D = 4.5\text{ A}, T_J = 175^\circ\text{C}$ $V_{GS} = 18\text{ V}, I_D = 4.5\text{ A}, T_J = 175^\circ\text{C}$	
C_{iss}	Input Capacitance		180		pF	$V_{DS} = 400\text{ V}, f = 1\text{ MHz}, V_{GS} = 0\text{ V}$	Fig. 8
C_{oss}	Output Capacitance		20				
C_{rss}	Reverse Transfer Capacitance		0.9				
Q_{gs}	Gate-Source Charge		2.3		nC	$V_{DD} = 400\text{ V}, I_D = 5\text{ A}, R_G = 10\ \Omega, V_{GS} = 0/15\text{ V}$	Fig. 7
Q_{gd}	Gate-Drain Charge		1.1				
Q_g	Total Gate Charge		11.2				
E_{on}	Turn-On Switching Energy		25				
E_{off}	Turn-Off Switching Energy		10		μJ		Fig. 12
$t_{d(on)}$	Turn-On Delay Time		5				
t_r	Rise Time		17		ns	$V_{DD} = 400\text{ V}, I_D = 5\text{ A}, R_G = 10\ \Omega, V_{GS} = -5/18\text{ V}$	
$t_{d(off)}$	Turn-Off Delay Time		8				
t_f	Fall Time		10				

Reverse SiC Diode Characteristics

Symbol	Parameter	Typ.	Max.	Unit	Test Conditions	Note
V_{SD}	Diode Forward Voltage	4.0		V	$V_{GS} = -4\text{ V}, I_{SD} = 2.5\text{ A}, T_J = 25^\circ\text{C}$	Fig. 16
		3.6			$V_{GS} = -4\text{ V}, I_{SD} = 2.5\text{ A}, T_J = 175^\circ\text{C}$	Fig. 17
$*I_{SD}$	Continuous Diode Forward Current		15	A	$TC = 25^\circ\text{C}$	
			12		$TC = 175^\circ\text{C}$	
t_{rr}	Reverse Recovery Time	50		ns	$I_{SD} = 5\text{ A}, di/dt = 1000\text{ A}/\mu\text{s}, V_{DD} = 400\text{ V}, V_{GS} = -5\text{ V}$	
Q_{rr}	Reverse Recovery Charge	38		nC		
I_{RRM}	Peak Reverse Recovery Current	2.4		A		

Thermal Characteristics

Symbol	Parameter	Typ.	Unit	Test Conditions	Note
R_{thJC}	Thermal Resistance from Junction to Case	2.88	$^\circ\text{C}/\text{W}$		Fig. 2
R_{thJA}	Thermal Resistance From Junction to Ambient	40			

Typical Characteristics




Figure 1. Safe Operating Area




Figure 2. Maximum Transient Thermal Impedance




Figure 3. Typical Output Characteristics, $T_J = 25^\circ\text{C}$




Figure 4. Typical Output Characteristics, $T_J = 175^\circ\text{C}$




Figure 5. Typical Transfer Characteristics




Figure 6. Total Power Dissipation

Figure 5. Typical Transfer Characteristics




Figure 7. Typical Gate Charge Characteristics




Figure 9. Typical Switching Energy vs. Supply Voltage




Figure 11. Switching Energy vs. Gate Resistance



Figure 6. Total Power Dissipation




Figure 8. Typical Capacitance Characteristics




Figure 10. Typical Switching Energy vs. Drain Current




Figure 12. Typical Switching Energy vs. Temperature






Figure 13. Breakdown Voltage vs. Temperature




Figure 14. Gate Threshold vs. Temperature




Figure 15. On-Resistance vs. Temperature




Figure 16. Body Diode Characteristics, $T_j = 25^\circ\text{C}$





Figure 17. Body Diode Characteristics, $T_j = 175^\circ\text{C}$

Package Outline Dimension: TO-220F (Full Pack)



SYMBOL	MILLIMETERS			NOTES	SYMBOL	MILLIMETERS			NOTES
	Normal	MIN.	MAX.			Normal	MIN.	MAX.	
A	4.4	4.2	4.6		e1	5.08	5	5.12	
A1	2.7	2.5	2.9		L	13.90	13.5	14.4	
b	0.8	0.7	0.9		L1	3.12	2.8	3.3	
b1	1.07	0.9	1.3		P	3.14	3.00	3.20	
b2	1.17	1	1.4		Q	2.44	2.3	2.6	
C	0.5	0.4	0.6		q	2.87	2.6	3	
D	15.63	15.4	15.8		W	0.37	0.3	0.5	
D1	6.22	6	6.4		T	1.52	1.3	1.7	
E	10.06	9.7	10.3		T1	1.20	1.1	1.3	
e	2.54	2.5	2.58						

Revision History

Revision	Date of Release	Description of Changes
Preliminary	2025-07-19	Initial Release

Information

For further information on technology, delivery terms and conditions and prices, please contact SUPSiC.

Disclaimer

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device. Hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non- infringement of intellectual property rights of any third party. 1 9.Sep. 2025 V 1.0 SUPSiC Copyright