

Features

- Effectively lower down T_j and R_{th} , high anti-EMI ability
- High speed switching with low capacitances
- High blocking voltage with low $R_{DS(on)}$
- Easy to drive and parallel
- RoHS compliant


Benefits

- Increased power density
- Higher operating frequency
- Reduced heat sink requirements
- Higher efficiency
- EMI reduction

Applications


- Power factor correction modules
- Switch mode power supplies
- Power inverters
- High voltage converters

Parameter	Rating	Units
V_{DS}	800	V
$I_D @ 25^\circ\text{C}$	12	A
$R_{DS(on)}$	360	m Ω



PDFN 5×6 Package

Part Number	Package	Marking
GC3M038065P	PDFN 5×6	GC3M038065



Maximum Ratings ($T_j = 25^\circ\text{C}$ unless otherwise specified)

Symbol	Parameter	Test conditions	Value	Unit
V_{DS}	Drain-Source Voltage		800	V
I_D	Continuous Drain Current	$T_c=25^\circ\text{C}$ $T_c=100^\circ\text{C}$	12 9	A
I_{DM}	Peak Drain Current	Pulse width tp limited by T_{jmax}	30	A
$V_{GS\ max}$	Gate-Source Voltage		-5/ 26	V
$V_{GS\ op}$	Recommend Gate-Source Voltage		0/ 18	V
P_{tot}	Power Dissipation	$T_c=25^\circ\text{C}$ $T_c=100^\circ\text{C}$	52 25	W
T_j	Operating Junction Temperature		-55~175	$^\circ\text{C}$
T_{stg}	Storage Temperature		-55~175	$^\circ\text{C}$

Electrical Characteristics ($T_c = 25^\circ\text{C}$ unless otherwise specified)

Symbol	Parameter	Min.	Typ.	Max.	Unit	Test Conditions	Note
$V_{(BR)DSS}$	Drain-Source Breakdown Voltage	800			V	$V_{GS} = 0\text{ V}, I_D = 1\text{ mA}$	
I_{DSS}	Zero Gate Voltage Drain Current		2	100	μA	$V_{GS} = 0\text{ V}, V_{DS} = 750\text{ V}$	
I_{GSS+}	Gate-Source Leakage Current			200	nA	$V_{DS} = 0\text{ V}, V_{GS} = +22\text{ V}$	
I_{GSS-}	Gate-Source Leakage Current			200	nA	$V_{DS} = 0\text{ V}, V_{GS} = -10\text{ V}$	
$V_{GS(th)}$	Gate Threshold Voltage		3.5	4.2	V	$V_{GS} = V_{DS}, I_{DS} = 1\text{ mA}, T_J = 25^\circ\text{C}$	Fig. 14
			2.8			$V_{GS} = V_{DS}, I_{DS} = 1\text{ mA}, T_J = 175^\circ\text{C}$	
$R_{DS(on)}$	Static Drain-Source On-Resistance		360 240	400 260	m Ω	$V_{GS} = 15\text{ V}, I_D = 6\text{ A}, T_J = 25^\circ\text{C}$ $V_{GS} = 18\text{ V}$	Fig. 15
			395 280			$V_{GS} = 15\text{ V}, I_D = 6\text{ A}, T_J = 175^\circ\text{C}$ $V_{GS} = 18\text{ V}$	
C_{iss}	Input Capacitance		208		pF	$V_{DS} = 400\text{ V}, f = 1\text{ MHz}, V_{GS} = 0\text{ V}$	Fig. 8
C_{oss}	Output Capacitance		18				
C_{rss}	Reverse Transfer Capacitance		1.8				
Q_g	Total Gate Charge		10.6		nC	$V_{DD} = 400\text{ V}, V_{GS} = -5/18\text{ V}, I_D = 5\text{ A}$	Fig. 7
Q_{gs}	Gate-Source Charge		5.1				
Q_{gd}	Gate-Drain Charge		2.2				
$R_{G(int)}$	Gate Input Resistance		1.2		Ω	$f = 1\text{ MHz}, I_D = 0\text{ A}$	
E_{on}	Turn-On Switching Energy		25		μJ	$V_{DD} = 400\text{ V}, I_D = 5\text{ A}, R_G = 10\text{ }\Omega, V_{GS} = -5/18\text{ V}$	Fig. 12
E_{off}	Turn-Off Switching Energy		10				
$t_{d(on)}$	Turn-On Delay Time		5		ns	$V_{DD} = 400\text{ V}, I_D = 5\text{ A}, R_G = 10\text{ }\Omega, V_{GS} = -5/18\text{ V}$	
t_r	Rise Time		17				
$t_{d(off)}$	Turn-Off Delay Time		8				
t_f	Fall Time		10				

Reverse SiC Diode Characteristics

Symbol	Parameter	Typ.	Max.	Unit	Test Conditions	Note
V_{SD}	Diode Forward Voltage	4.0		V	$V_{GS} = -4\text{ V}, I_{SD} = 5\text{ A}, T_J = 25^\circ\text{C}$	Fig. 16
		3.6			$V_{GS} = -4\text{ V}, I_{SD} = 5\text{ A}, T_J = 175^\circ\text{C}$	Fig. 17
$*I_{SD}$	Continuous Diode Forward Current		12	A	$TC = 25^\circ\text{C}$	
			8		$TC = 175^\circ\text{C}$	
t_{rr}	Reverse Recovery Time	50		ns	$I_{SD} = 5\text{ A}, di/dt = 1000\text{ A}/\mu\text{s}, V_{DD} = 400\text{ V}, V_{GS} = -5\text{ V}$	
Q_{rr}	Reverse Recovery Charge	38		nC		
I_{RRM}	Peak Reverse Recovery Current	2.4		A		

Thermal Characteristics

Symbol	Parameter	Typ.	Unit	Test Conditions	Note
R_{thJC}	Thermal Resistance from Junction to Case	2.88	$^\circ\text{C}/\text{W}$		Fig. 2
R_{thJA}	Thermal Resistance From Junction to Ambient	40			

Typical Characteristics




Figure 1. Safe Operating Area




Figure 2. Maximum Transient Thermal Impedance




Figure 3. Typical Output Characteristics, $T_J = 25^\circ\text{C}$




Figure 4. Typical Output Characteristics, $T_J = 175^\circ\text{C}$




Figure 5. Typical Transfer Characteristics




Figure 6. Total Power Dissipation

Figure 5. Typical Transfer Characteristics




Figure 7. Typical Gate Charge Characteristics




Figure 9. Typical Switching Energy vs. Supply Voltage




Figure 11. Switching Energy vs. Gate Resistance

Figure 6. Total Power Dissipation




Figure 8. Typical Capacitance Characteristics




Figure 10. Typical Switching Energy vs. Drain Current




Figure 12. Typical Switching Energy vs. Temperature




Figure 13. Breakdown Voltage vs. Temperature




Figure 14. Gate Threshold vs. Temperature




Figure 15. On-Resistance vs. Temperature




Figure 16. Body Diode Characteristics, $T_j = 25^\circ\text{C}$




Figure 17. Body Diode Characteristics, $T_j = 175^\circ\text{C}$

Package Outline Dimension: PDFN 5×6

Technical drawing of a package showing three views: top, side, and bottom.

- Top View:** Shows a rectangular package with a central circular feature. Dimensions include **L** (total width), **L1** (width of the central feature), and **L2** (width of the side flaps).
- Side View:** Shows the profile of the package. Dimensions include **A** (height), **C** (thickness), and **C1** (width of the base).
- Bottom View:** Shows the underside of the package. Dimensions include **B** (width of the side flaps), **E** (height of the side flaps), and **R** (radius of the corner).

Dim.	Min.	Max.
A	4.8	5.2
B	0.25	0.35
C	1.0	1.2
C1	Typ 0.254	
C2	Typ 0.254	
E	Typ 1.27	
L	6.0	6.3
L1	5.7	6.0
L2	MAX 0.2	
R	Typ 13°	

All Dimensions in millimeter

Revision History

Revision	Date of Release	Description of Changes
Preliminary	2025-07-19	Initial release
	18. Sep. 2025	Official version release

Information

For further information on technology, delivery terms and conditions and prices, please contact SUPSiC.

Disclaimer

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device. Hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party.