




REVISION			
LTR	DESCRIPTION	DATE	APP
A0	NEW RELEASE	04/11/2023	PECK


- NOTES:
- ELECTRICAL CHARACTERISTICS:
 - CONTACT CURRENT RATING: 0.5 AMPERE MAX. PER PIN.
 - VOLTAGE RATING: 50V AC.
 - INSULATION RESISTANCE :500 MEGAOHMS MIN. AT 500V DC.
 - DIELECTRIC WITHSTANDING VOLTAGE: 300V AC RMS AT 60Hz, FOR 1 MINUTE.
 - CONTACT RESISTANCE: 55 MILLIOHMS MAX. PER PIN INITIAL.
R=20 MILLIOHMS MAX. PER PIN AFTER FULL ENVIRONMENT TESTING.
 - MECHANICAL CHARACTERISTICS: DURABILITY:60 MATING CYCLES.
 - OPERATION TEMPERATURE:-40°C TO +80°C.
 - RECOMMENDED PROCESS CONDITION: SMT, PEAK TEMPERATURE: 260.°C, 10~20S.


H
3.2mm
4.2mm

DIMENSION CLASSIFICATION		台灣碩方精密電子科技有限公司		TAIWAN SOFNG PRECISION ELECTRONIC CO., LTD		開關, 連接器		SOFNG	
■	CRITICAL	TITLE		PCIE-67C32H M.2连接器		67PIN 二一分结构		PART NO.	
☒	MAJOR	TOLERANCE TABLE		.X		± 0.40		APPROVED	
				.XX		± 0.25		CHECKED	
				.XXX		± 0.10		DRAWIN	
				ANGLE		± 2°		REV	
								SCALE 1:1	
								UNIT mm	
								SIZE A4	
								SHEET NO. 1/3	




ITEM	DESCRIPTION	MATERIAL	Q'TY	TREATMENT
4	PI-FILM	POLYIMIDE	1	BROWN COLOR
3	METAL TAB	STAINLESS STEEL (SUS301)	2	10u" NICKEL UNDER PLATING 100u" MATTE TIN PLATING OVER ALL
2	CONTACT	PHOSPHOR BRONZE (C5210R-SH)	67	50u" NICKEL UNDER PLATING GOLD FLASH PLATING AT TAIL AREA GOLD FLASH OR 5u" GOLD PLATING OR 10" GOLD PLATING OR 15u" GOLD PLATING OR 30u" GOLD PLATING AT CONTACT AREA
1	HOUSING	LCP (SV6808THF)	1	UL94V-0, HALOGEN FREE, BLACK COLOR

DIM.Z MAX.(mm)	MODULE TYPE
3.55	S1&D1
3.70	S2&D2
3.85	S3&D3&D4
4.10	S4
4.35	S5





REVISION			
LTR	DESCRIPTION	DATE	APP
A0	NEW RELEASE	04/11/2023	PECK



DIMENSION CLASSIFICATION		台灣碩方精密電子科技有限公司 TAIWAN SOFNG PRECISION ELECTRONIC CO., LTD			
■	CRITICAL	TITLE PCIE-67C32H M.2连接器 67PIN 二一分结构			
☒	MAJOR				
TOLERANCE TABLE		PART NO.	PCIE-67C32H		
.X	± 0.40	APPROVED	Peck	DWG NO.	SERIES SD106
.XX	± 0.25	CHECKED	Paul	SCALE 1:1	UNIT mm
.XXX	± 0.10	DRAWIN	David	REV A0	SIZE A4
ANGLE	± 2°			REV	SHEET NO. 3/3