









CUSTOMER DRAWING		东莞市文章济美电子有限公司	
Tolerance Unspecified (未注公差)		Size(图幅):	
0.0 ±0.25 0°. ±5°		Unit(单位):	
0.00 ±0.15 0°0. ±3°		MM	
0.000 ±0.10 0°0.0 ±1°		Scale(比例):	
		1 : 1	
Project View (投影视图)		Page(页数):	
		1 OF 3	
Rev(版本):		Designer(设计):	
A		吴小光	
		Checked(审核):	
		Approved(核准):	
		Product Name(产品名称): 0.5Pitch H=2.30 M.2 CARD CONNECTOR B KEY 2.3H TYPE Product No(产品料号): 5001-C10-S67RIA-T0	







HOW TO MATE AND EXTRACT

MATE: ① → ④

EXTRACT: ⑤


NOTE: Mating force will generate from step 3 to step 4.

CUSTOMER DRAWING				东莞市文章济美电子有限公司		
Tolerance Unspecified (未注公差)		Size (图幅):		Product Name (产品名称):		
0.0 ±0.25 0° ±5°		Unit (单位):		0.5 Pitch H=2.30 M.2 CARD CONNECTOR B KEY 2.3H TYPE		
0.00 ±0.15 0° 0 ±3°		MM		Product No (产品料号):		
0.000 ±0.10 0° 00 ±1°		Scale (比例):		5001-C10-S67RIA-T0		
1:1		Page (页数):		Designer (设计):		
Project View (投影视角)		2 OF 3		吴小光		
Rev (版本):		A		Checked (审核):		
A		Original Issue		Approved (核准):		
Rev 版本		Change Description 变更内容				
Date 日期		Revisor 制/修订人				
2023/10/19		吴小光				




CUSTOMER DRAWING		东莞市文章济美电子有限公司		
Tolerance Unspecified (未注公差)		Size(图幅):	Product Name(产品名称):	
0.0 ±0.25 0° ±5°	Unit(单位):	0.5Pitch H=2.30 M.2 CARD CONNECTOR B KEY 2.3H TYPE		
0.00 ±0.15 0° 0 ±3°	MM	Product No(产品料号):		
0.000 ±0.10 0° 00 ±1°	Scale(比例):	5001-C10-S67RIA-T0		
1:1	Project View (投影视角)	Page(页数):	Designer(设计):	
	3 OF 3	Rev(版本):	Checked(审核):	Approved(核准):
		A	吴小光	

A	Original Issue	2023/10/19	吴小光
Rev 版本	Change Description 变更内容	Date 日期	Revisor 制/修订人



- NOTES:
- 1. 10 SPROCKET HOLE PITCH CUMULATIVE TOLERANCE. $\pm 0.20\text{mm}$
 - 2. CARRIER CAMBER NOT TO EXCEED 1mm IN 250mm.
 - 3. ALL DIMENSIONS MEET EIA-481-C REQUIREMENTS.
 - 4. MATERIAL: WHITE ANTI-STATIC POLYSTYRENE.
 - 5. THICKNESS: $0.30 \pm 0.05 \text{ mm}$.
 - 6. PACKING LENGTH PER 13" REEL : 19.80METERS.
 - 7. COMPONENT LOAD PER 13" REEL : 1200PCS.
 - 8. PEELING OFF FORCE OF TOP TAPE 0.1N~0.7N(10.2gf~71.4gf).



PULL OUT DIRECTION

160 Min
Tail Part (Empty)

Component
Supplier



100 Min
Top tape bonded part(Empty)

400 Min
Top tape leader part



PEEL OFF DIRECTION

10°

PULL OUT DIRECTION



DETAIL B



CLASSIFICATION DIMENSION (尺寸类别): FAI (首次检验): @ To @ ■ MARK IS MAJOR DIM (重点尺寸标示) ● MARK IS CRITICAL DIM (Cpk&Cp 标示)				东莞市文章济美电子有限公司			
Tolerance Unspecified (未注公差) 0.0 ±0.10 0° ±3° 0.00 ±0.05 0° 0 ±2° 0.000 ±0.02 0° 00 ±1°				Product Name (产品名称): 0.5Pitch H=2.3 NGFF (M.2) Key M 插拔卧式2代. 载带			
Size (图幅): A4 Unit (单位): MM Scale (比例): 1:1				Product No (产品料号): EB-750221300-01 (ANC03)			
Project View (投影视角) 1 OF 1 Rev (版本): 1.0				Drawing No (图面编号): DNE00****		Date (日期): 2024/03/12	
Rev (版本): 1.0		Change Description (变更内容)		Designer (设计): 吴小光		Checked (审核): 吴小光	
Date (日期): 2024/03/12		Revisor (修订人): 吴小光		Approved (核准):			