

CMDG65R245/CMUG65R245

650V, 255mΩ typ., 15A N-Channel Silicon Carbide Power MOSFET

General Description

This silicon carbide Power MOSFET device has been developed using Cmos's advanced SiC MOSFET technology. The device features a very low $R_{DS(on)}$ over the entire temperature range combined with low capacitances and very high switching operations, which improve application performance in frequency, energy efficiency, system size and weight reduction.

Features

- 100% Avalanche Tested
- Optimized switching with a low gate charge
- Fast intrinsic diode with low reverse recovery
- RoHS Compliant


Product Summary

BVDSS	$R_{DS(on)}$ max.	ID
650V	290mΩ	15A

Applications

- Low power system, SMPS
- Adapter, LED power, TV display

TO-252/TO-251 Pin Configuration



Absolute Maximum Ratings

Symbol	Parameter	Rating	Units
V_{DS}	Drain-Source Voltage	650	V
V_{GS}	Absolute maximum values	-10/+22	V
V_{GSop}	Recommended operational values	0/+18	V
$I_D@T_C=25^{\circ}C$	Continuous Drain Current	15	A
$I_D@T_C=100^{\circ}C$	Continuous Drain Current	10.5	A
I_{DM}	Pulsed Drain Current	45	A
EAS	Single Pulse Avalanche Energy (Note 1)	151	mJ
$P_D@T_C=25^{\circ}C$	Total Power Dissipation	75	W
T_{STG}	Storage Temperature Range	-55 to 175	$^{\circ}C$
T_J	Operating Junction Temperature Range	-55 to 175	$^{\circ}C$

Thermal Data

Symbol	Parameter	Typ.	Max.	Unit
$R_{\theta JA}$	Thermal Resistance Junction-ambient	---	40	$^{\circ}C/W$
$R_{\theta JC}$	Thermal Resistance Junction-case	---	2	$^{\circ}C/W$

CMDG65R245/CMUG65R245

650V, 255mΩ typ., 15A N-Channel Silicon Carbide Power MOSFET

Electrical Characteristics (T_J=25°C , unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
BV _{DSS}	Drain-Source Breakdown Voltage	V _{GS} =0V, I _D =1mA	650	---	---	V
R _{DS(ON)}	Static Drain-Source On-Resistance	V _{GS} =18V, I _D =5A	---	255	290	mΩ
		V _{GS} =18V, I _D =5A, T _J =175°C	---	265	---	
		V _{GS} =15V, I _D =5A	---	366	---	
		V _{GS} =15V, I _D =5A, T _J =175°C	---	335	---	
V _{GS(th)}	Gate Threshold Voltage	V _{GS} =V _{DS} , I _D =2mA (tested after V _{GS} =22V, 1ms pulse)	2.0	3.1	5.0	V
I _{DSS}	Drain-Source Leakage Current	V _{DS} =650V, V _{GS} =0V	---	1	50	μA
		V _{DS} =650V, V _{GS} =0V, T _J =175°C	---	20	---	
I _{GSS}	Gate-Source Leakage Current	V _{GS} =+22V, V _{DS} =0V	---	---	+250	nA
		V _{GS} =-10V, V _{DS} =0V	---	---	-250	
R _g	Gate Resistance	V _{DS} =0V, V _{GS} =0V, f=1MHz	---	3.9	---	Ω
Q _{g(tot)}	Total Gate Charge	V _{DS} =500V, I _D =5A V _{GS} =0V to 18V	---	10.5	---	nC
Q _{gs}	Gate-Source Charge		---	2.4	---	
Q _{gd}	Gate-Drain Charge		---	3.4	---	
E _{oss}	Stored Energy in Output Capacitance	V _{GS} =0V, V _{DS} =0V to 500V	---	4.1	---	μJ
C _{o(er)}	Energy Related Output Capacitance		---	33	---	pF
C _{o(tr)}	Time Related Output Capacitance		---	47	---	
E _{on}	Turn-on Switching Energy	V _{DS} =500V I _D =5A V _{GS} =0V / 18V	---	27.4	---	μJ
E _{off}	Turn-off Switching Energy		---	7.6	---	
E _{tot}	Total Switching Energy		---	35	---	
T _{d(on)}	Turn-On Delay Time	R _G =10Ω FWD = 650V 4A SiC Diode Inductive load	---	7	---	ns
T _r	Rise Time		---	13.5	---	
T _{d(off)}	Turn-Off Delay Time		---	15	---	
T _f	Fall Time		---	10	---	
C _{iss}	Input Capacitance	V _{DS} =100V, V _{GS} =0V, f=1MHz	---	240	---	pF
C _{oss}	Output Capacitance		---	65	---	
C _{rss}	Reverse Transfer Capacitance		---	14	---	

Diode Characteristics

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
I _S	Continuous Source Current	V _G =V _D =0V, Force Current	---	---	15	A
I _{SM}	Pulsed Source Current		---	---	45	A
V _{SD}	Diode Forward Voltage	V _{GS} =0V, I _{SD} =5A, T _J =25°C	---	4.6	---	V
t _{rr}	Reverse Recovery Time	di/dt=600A/μs, Includes Q _{oss} V _{DD} =500V, I _{SD} =5A, T _J =25°C	---	8.6	---	ns
Q _{rr}	Reverse Recovery Charge		---	13.4	---	nC
I _{rrm}	Peak Reverse Recovery Current		---	2.6	---	A

Note :

1.The EAS data shows Max. rating . The test condition is V_{DD}=100V, V_{GS}=10V, L=10mH, I_{AS}=5.5A.

This product has been designed and qualified for the consumer market.







CMOS assumes no liability for customers' product design or applications.

CMOS reserves the right to improve product design, functions and reliability without notice. Please refer to the latest version of specification.

CMDG65R245/CMUG65R245

650V, 255mΩ typ., 15A N-Channel Silicon Carbide Power MOSFET





Typical Characteristics



CMDG65R245/CMUG65R245

650V, 255mΩ typ., 15A N-Channel Silicon Carbide Power MOSFET

Typical Characteristics




CMDG65R245/CMUG65R245

650V, 255mΩ typ., 15A N-Channel Silicon Carbide Power MOSFET

Package Dimension

TO-252

Unit :mm



注:

1. 塑封体未标注为光面 $R_a=0.1$; 亚光面 $R_a=1.0 \sim 1.2$
2. 未注公差 ± 0.15 未标注圆角 $R_{max}=0.25$
3. 塑封体无缺损、缩孔、裂纹、气泡等不良缺陷
4. 标注单位mm
5. 顶针孔不允许凸出塑封体表面

CMDG65R245/CMUG65R245

650V, 255mΩ typ., 15A N-Channel Silicon Carbide Power MOSFET

Package Dimension

TO-251A

Unit :mm

