


DESCRIPTION

- Collector-Emitter Breakdown Voltage
 $-V_{(BR)CEO} = 120V(\text{Min})$
- Collector-Emitter Saturation Voltage
 $-V_{CE(sat)}: 0.5V(\text{Max}) @ I_C = 1A$
- Complement to Type
 MJE15028G-JSM (NPN)
 MJE15029G-JSM (PNP)

APPLICATIONS

- High-Frequency Audio Amplifiers



ABSOLUTE MAXIMUM RATINGS($T_a=25^{\circ}\text{C}$)

SYMBOL	PARAMETER	VALUE	UNIT
V_{CBO}	Collector-Base Voltage	120	V
V_{CEO}	Collector-Emitter Voltage	120	V
V_{EBO}	Emitter-Base Voltage	5	V
I_C	Collector Current-Continuous	8	A
I_{CM}	Collector Current-Peak	16	A
I_B	Base Current-Continuous	2	A
P_C	Total Power Dissipation @ $T_c=25^{\circ}\text{C}$	50	W
T_J	Junction Temperature	-65~150	$^{\circ}\text{C}$
T_{stg}	Storage Temperature Range	-65~150	$^{\circ}\text{C}$

THERMAL CHARACTERISTICS

SYMBOL	PARAMETER	MAX	UNIT
$R_{th\ j-c}$	Thermal Resistance, Junction to Case	2.5	$^{\circ}\text{C/W}$

ELECTRICAL CHARACTERISTICS ($T_C=25^{\circ}\text{C}$ unless otherwise specified)


SYMBOL	PARAMETER	CONDITIONS	MIN	TYP	MAX	UNIT
$V_{(BR)CEO}$	Collector-Emitter Breakdown Voltage	$I_C=10\text{mA}$, $I_B=0\text{A}$	120	--	--	V
I_{CEO}	Collector Cutoff Current	$V_{CE}=120\text{V}$, $I_B=0\text{A}$	--	--	0.1	mA
I_{CBO}	Collector Cutoff Current	$V_{CB}=120\text{V}$, $I_E=0\text{A}$	--	--	10	μA
I_{EBO}	Emitter Cutoff Current	$V_{EB}=5\text{V}$, $I_C=0\text{A}$	--	--	10	μA
h_{FE1}	DC Current Gain	$I_C=0.1\text{A}$, $V_{CE}=2\text{V}$	40	--	--	--
h_{FE2}	DC Current Gain	$I_C=2\text{A}$, $V_{CE}=2\text{V}$	40	--	--	--
h_{FE3}	DC Current Gain	$I_C=3\text{A}$, $V_{CE}=2\text{V}$	40	--	--	--
h_{FE4}	DC Current Gain	$I_C=4\text{A}$, $V_{CE}=2\text{V}$	20	--	--	--
$V_{CE(sat)}$	Collector-Emitter Saturation Voltage	$I_C=1\text{A}$, $I_B=0.1\text{A}$	--	--	0.5	V
$V_{BE(on)}$	Base-Emitter On Voltage	$I_C=1\text{A}$, $V_{CE}=2\text{V}$	--	--	1.0	V

Ordering Information

Order number	Package	Marking	Operation Temperature Range	MSL Grade	Ship,Quantity	Green
MJE15028G-JSM	TO-220-3	MJE15028G	-65 to 150°C	1	Tube,1000	Rohs
MJE15029G-JSM	TO-220-3	MJE15029G	-65 to 150°C	1	Tube,1000	Rohs

Package Information

TO-220-3



Unit: mm

Symbol	Size		Symbol	Size		Symbol	Size		Symbol	Size	
	Min	Max		Min	Max		Min	Max		Min	Max
W	9.66	10.28	W5	9.80	10.20	L4**	6.20	6.60	T3	0.45	0.60
W1	2.54 (TYP)		L	9.00	9.40	L5	2.79	3.30	G(Φ)	3.50	3.70
W2	0.70	0.95	L1	6.40	6.80	T	4.30	4.70			
W3	1.17	1.37	L2	2.70	2.90	T1	1.15	1.40			
W4*	1.32	1.72	L3	12.70	14.27	T2	2.20	2.60			

Revision History

Rev.	Change	Date
V1.0	Initial version	6/27/2019

Important Notice

JSMSEMI Semiconductor (JSMSEMI) PRODUCTS ARE NEITHER DESIGNED NOR INTENDED FOR USE IN MILITARY AND/OR AEROSPACE, AUTOMOTIVE OR MEDICAL DEVICES OR SYSTEMS UNLESS THE SPECIFIC JSMSEMI PRODUCTS ARE SPECIFICALLY DESIGNATED BY JSMSEMI FOR SUCH USE. BUYERS ACKNOWLEDGE AND AGREE THAT ANY SUCH USE OF JSMSEMI PRODUCTS WHICH JSMSEMI HAS NOT DESIGNATED FOR USE IN MILITARY AND/OR AEROSPACE, AUTOMOTIVE OR MEDICAL DEVICES OR SYSTEMS IS SOLELY AT THE BUYER' S RISK.

JSMSEMI assumes no liability for application assistance or customer product design. Customers are responsible for their products and applications using JSMSEMI products.

Resale of JSMSEMI products or services with statements diferent from or beyond the parameters stated by JSMSEMI for that product or service voids all express and any implied warranties for the associated JSMSEMI product or s ervice. JSMSEMI is not responsible or liable for any such statements.

JSMSEMI All Rights Reserved. Information and data in this document are owned by JSMSEMI wholly and may not be edited, reproduced, or redistributed in any way without the express written consent from JSMSEMI.

Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the JSMSEMI product that you intend to use.

For additional information please contact Kevin@jsmsemi.com or visit www.jsmsemi.com