



Features

- Total power dissipation: Max.300mW
- Wide zenerreverse voltage range 2.0V to 75V
- Small plastic package suitable for surface mounted design
- Tolerance approximately $\pm 5\%$

Features

- Case: SOD-323
- Terminals: Solderable per MIL-STD-750,Method 2026
- Approx. Weight: 5.48mg / 0.00019oz



SOD-323



Package Marking and Ordering Information

Product ID	Pack	Marking	Qty(PCS)
MM3ZxxT1GX	SOD-323	XX	3000

XX=Device code, see table on page2 the marking code.

The marking bar indicates the cathode.

Absolute Maximum Ratings($T_a=25^{\circ}\text{C}$)

Characteristic	Symbol	Value	Unit
Forward voltage @ $I_F=10\text{mA}$	V_F	0.9	V
Power Dissipation	P_{tot}	300	mW
Typical thermal resistance junction to ambient ¹	$R_{\theta JA}$	417	$^{\circ}\text{C/W}$
Junction Temperature	T_j	150	$^{\circ}\text{C}$
Storage Temperature Range	T_{stg}	-55 ~ +150	$^{\circ}\text{C}$

(1) Thermal resistance from junction to ambient at P.C.B. mounted with 2.0" X 2.0" (5 X 5 cm) copper areas pads.



Electrical Characteristics (Ta=25°C unless otherwise specified)

Type	Marking	Zener Voltage Range ⁽¹⁾				Dynamic Impedance	Reverse Current	
		V _{ZT} (at I _{ZT})			I _{ZT}	Z _{ZT} (at I _{ZT})	I _R	at V _R
		Min (V)	Nom (V)	Max (V)	(mA)	Max (Ω)	Max (μA)	(V)
MM3Z2V0T1GX	B0	1.8	2.0	2.15	5	100	120	0.5
MM3Z2V2T1GX	C0	2.08	2.2	2.33	5	100	120	0.7
MM3Z2V4T1GX	1C	2.28	2.4	2.56	5	100	120	1
MM3Z2V7T1GX	1D	2.5	2.7	2.9	5	110	120	1
MM3Z3V0T1GX	1E	2.8	3.0	3.2	5	120	50	1
MM3Z3V3T1GX	1F	3.1	3.3	3.5	5	130	20	1
MM3Z3V6T1GX	1H	3.4	3.6	3.8	5	130	10	1
MM3Z3V9T1GX	1J	3.7	3.9	4.1	5	130	5	1
MM3Z4V3T1GX	1K	4	4.3	4.6	5	130	5	1
MM3Z4V7T1GX	1M	4.4	4.7	5	5	130	2	1
MM3Z5V1T1GX	1N	4.8	5.1	5.4	5	130	2	1.5
MM3Z5V6T1GX	1P	5.2	5.6	6	5	80	1	2.5
MM3Z6V2T1GX	1R	5.8	6.2	6.6	5	50	1	3
MM3Z6V8T1GX	1X	6.4	6.8	7.2	5	30	0.5	3.5
MM3Z7V5T1GX	1Y	7	7.5	7.9	5	30	0.5	4
MM3Z8V2T1GX	1Z	7.7	8.2	8.7	5	30	0.5	5
MM3Z9V1T1GX	2A	8.5	9.1	9.6	5	30	0.5	6
MM3Z10VT1GX	2B	9.4	10	10.6	5	30	0.1	7
MM3Z11VT1GX	2C	10.4	11	11.6	5	30	0.1	8
MM3Z12VT1GX	2D	11.4	12	12.7	5	35	0.1	9
MM3Z13VT1GX	2E	12.4	13	14.1	5	35	0.1	10
MM3Z15VT1GX	2F	13.8	15	15.6	5	40	0.1	11
MM3Z16VT1GX	2H	15.3	16	17.1	5	40	0.1	12
MM3Z18VT1GX	2J	16.8	18	19.1	5	45	0.1	13
MM3Z20VT1GX	2K	18.8	20	21.2	5	50	0.1	15
MM3Z22VT1GX	2M	20.8	22	23.3	5	55	0.1	17
MM3Z24VT1GX	2N	22.8	24	25.6	5	60	0.1	19
MM3Z27VT1GX	2P	25.1	27	28.9	2	70	0.1	21
MM3Z30VT1GX	2R	28	30	32	2	80	0.1	23
MM3Z33VT1GX	2X	31	33	35	2	80	0.1	25
MM3Z36VT1GX	2Y	34	36	38	2	90	0.1	27
MM3Z39VT1GX	2Z	37	39	41	2	100	0.1	30
MM3Z43VT1GX	3A	40	43	46	2	130	0.1	33
MM3Z47VT1GX	3B	44	47	50	2	150	0.1	36
MM3Z51VT1GX	3C	48	51	54	2	180	0.1	39
MM3Z56VT1GX	3D	52	56	60	2	200	0.1	43
MM3Z62VT1GX	3E	58	62	66	2	215	0.1	47
MM3Z68VT1GX	3F	64	68	72	2	240	0.1	52
MM3Z75VT1GX	3H	70	75	79	2	265	0.1	56

(1) V_{ZT} is tested with pulses (20 ms)



Typical Characteristics

Fig.1 Maximum Continuous Power Derating






Fig.2 Typical Transient Thermal Impedance





SOD-323 Package Outline Dimensions



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A		1.100		0.043
A1	0.000	0.100	0.000	0.004
A2	0.800	1.000	0.031	0.039
b	0.250	0.350	0.010	0.014
c	0.080	0.150	0.003	0.006
D	1.200	1.400	0.047	0.055
E	1.600	1.800	0.063	0.071
E1	2.500	2.750	0.098	0.108
L	0.475 REF		0.019 REF	
L1	0.250	0.400	0.010	0.016
θ	0°	8°	0°	8°



Attention

- Any and all HUA XUAN YANG ELECTRONICS products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your HUA XUAN YANG ELECTRONICS representative nearest you before using any HUA XUAN YANG ELECTRONICS products described or contained herein in such applications.
- HUA XUAN YANG ELECTRONICS assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein.
- Specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.
- HUA XUAN YANG ELECTRONICS CO.,LTD. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.
- In the event that any or all HUA XUAN YANG ELECTRONICS products(including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.
- No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of HUA XUAN YANG ELECTRONICS CO.,LTD.
- Information (including circuit diagrams and circuit parameters) herein is for example only ; it is not guaranteed for volume production. HUA XUAN YANG ELECTRONICS believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.
- Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the HUA XUAN YANG ELECTRONICS product that you intend to use.