








RECOMMENDED P.C.B LAYOUT
T=±0.05



NOTE:
1.MATERIAL:
HOUSING: LCP 30% G/F UL 94V-0 ;BLACK
CONTACT(1.27): C5191R-H,T=0.30±0.01mm
CONTACT(0.8): C5191R-H,T=0.25±0.01mm
PEG: C2680R-H,T=0.30±0.01mm
2.MECHANICAL:
MATING: 25N MAX.
WITHDRAWAL FORCE: 5N MIN.
DURABILITY: 500 CYCLES.
3.ELECTRICAL:
CURRENT RATING: 1.5 A
CONTACT RESISTANCE:30 Milliohms MAX.
INSULATION RESISTANCE: 1000 Megohms MIN.
WITHSTANDING VOLTAGE: 500 VAC
4.FINISH:
CONTACT: 1u" GOLD MIN. PLATING ON CONTACT AREA
100u"MIN. TIN PLATING ON SOLDER TAILS
50u" MIN. NICKEL UNDERPLATING OVER ALL
PEG:100u" MIN. TIN PLATING ON SOLDER AREA
50u" MIN.NICKEL UNDERPLATING OVER ALL
5.ENVIRONMENTAL:
OPERATURE RANGE:-25°C TO +85°C
6.PART NUMBER

2ST F 004 A 029 ** 02 1 4

包装方式: 1:Reel Packang(卷装) 加CAP
4. TUBE PACKAGE(管装)
颜色: BLACK (黑色)
电镀码: 半金亮锡E0 = FLASH ,
E1 = 1u", E2 = 3u", E3 = 5u",
E4 = 10u", E5 = 15u",

				.X ±0.30	.X° ±1.0°
				.XX ±0.25	.XX° ±0.5°
				.XXX ±0.20	.XXX° ±0.2°
1.1					SCALE 1:1 UNIT mm
REV:	ECN. NO	DR. BY	DATE	PAGE: 1/1	REV: 1.0

东莞市文章济美电子有限公司

Title: SAS 29PIN 母座180° SMT(双柱)倒角直立式		Approved:
Part No.: 5001-2STF004A029E50214-B		Checked:
Part Name:	Material:	Drawn: TONY JIANG
Drawing No.:	Mode NO.:	Date: 2012-02-11