




NOTE:

1.MATERIAL:
HOUSING: LCP 30% G/F UL 94V-0 ;BLACK
CONTACT(1.27): C5191R-H,T=0.30±0.01mm
CONTACT(0.8): C5191R-H,T=0.25±0.01mm
PEG: C2680R-H,T=0.30±0.01mm

2.MECHANICAL:
MATING: 59N MAX.
WITHDRAWAL FORCE: 5N MIN.
DURABILITY: 500 CYCLES.

3.ELECTRICAL:
CURRENT RATING: 1.5 A
CONTACT RESISTANCE:30 Milliohms MAX.
INSULATION RESISTANCE: 1000 Megohms MIN.
WITHSTANDING VOLTAGE: 500 VAC

4.FINISH:
CONTACT: 1u" GOLD MIN. PLATING ON CONTACT AREA
100u"MIN. TIN PLATING ON SOLDER TAILS
50u" MIN. NICKEL UNDERPLATING OVER ALL
PEG:100u" MIN. TIN PLATING ON SOLDER AREA
50u" MIN.NICKEL UNDERPLATING OVER ALL

5.ENVIRONMENTAL:
OPERATURE RANGE:-25°C TO +85°C

东莞市文章济美电子有限公司

Part Name: PCIe 68pin + 2 PIN 母座 SMT CONNECTOR

Part No.: 5001-2STF001A068E50013-B

Title: Material: Drawn: 骆志旺

Drawing No.: Mode NO.: Date: 2017-12-21