

Technical drawing of a mechanical assembly, showing five views (1 to 5) and dimensions in millimeters.

View 1 (Top View): Overall length 45.60, inner length 41.90, hole spacing 0.40±0.05, hole diameter 1.70.


View 2 (Front View): Overall length 37.75, hole diameter 1.20, hole diameter 0.80, hole spacing 0.70, hole diameter 4.70, hole diameter 1.70, hole diameter 40.43, hole diameter 36.19.

View 3 (Side View): Overall length 33.69, hole spacing 1.27, hole spacing 1.90, hole spacing 8.25, hole spacing 7.62, hole diameter 1.15, hole diameter 1.40, hole diameter 0.48, hole diameter 1.90±0.25.


View 4 (Bottom View): Overall length 17.78, hole diameter 0.20.

View 5 (Isometric View): Isometric representation of the assembly.

GENERAL T	
DIM.	
.X	
.XX	
.XXX	
GENERAL	
.X°	
.XX°	
.XXX°	



30u" NICKEL UNDERPLATING OVER ALL

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD				BXCONN [®]	
DIM. TOL. .X ±0.30 .XX ±0.20 .XXX ±0.05 GENERAL ANGLE: .X° ±3° .XX° ±2° .XXX° ±0.5°		TITLE: SATA 7+15P 直立式SMT 带接地片					
		DWG. NO.: SATA-22M-22HM01		CHECKED: MAX			
		PART NO.: SATA-22M-22HM01		DRAWN: ELLA			
		UNIT: mm	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn	APPROVED: WILL