









Part No	CKT	A	B	C	D
XY-HY2.0-2A21-BL	2	2.0	6.0	4.84	2.4
XY-HY2.0-3A21-BL	3	4.0	8.0	6.84	2.4
XY-HY2.0-4A21-BL	4	6.0	10.0	8.84	4.4
XY-HY2.0-5A21-BL	5	8.0	12.0	10.84	6.4
XY-HY2.0-6A21-BL	6	10.0	14.0	12.84	8.4
XY-HY2.0-7A21-BL	7	12.0	16.0	14.84	10.4
XY-HY2.0-8A21-BL	8	14.0	18.0	16.84	12.4
XY-HY2.0-9A21-BL	9	16.0	20.0	18.84	14.4
XY-HY2.0-10A21-BL	10	18.0	22.0	20.84	16.4
XY-HY2.0-11A21-BL	11	20.0	24.0	22.84	18.4
XY-HY2.0-12A21-BL	12	22.0	26.0	24.84	20.4
XY-HY2.0-13A21-BL	13	24.0	28.0	26.84	22.4
XY-HY2.0-14A21-BL	14	26.0	30.0	28.84	24.4
XY-HY2.0-15A21-BL	15	28.0	32.0	30.84	26.4
XY-HY2.0-16A21-BL	16	30.0	34.0	32.84	28.4
XY-HY2.0-17A21-BL	17	32.0	36.0	34.84	30.4
XY-HY2.0-18A21-BL	18	34.0	38.0	36.84	32.4
XY-HY2.0-19A21-BL	19	36.0	40.0	38.84	34.4
XY-HY2.0-20A21-BL	20	38.0	42.0	40.84	36.4





技术指标(Technical Index):

- 1.温度范围(Temperature range): $-25^{\circ}\text{C}\sim+85^{\circ}\text{C}$.
- 2.额定电压(Rated voltage):200V,AC.
- 3.额定电流(Rated current):2.0A AC,DC.
- 4.接触电阻(Contact resistance): $\leq 25\text{m}\Omega$.
- 5.绝缘电阻(Insulation resistance): $\geq 1000\text{M}\Omega$.
- 6.耐压值(Withstanding voltage):1000V AC/minute.




序号	品名	材质
①	HY2.0弯针WTB胶芯	LCP UL94V-0 本色
②	HY2.0弯针WTB端子	铜合金/表面镀锡

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X $\pm$ 0.5	X.* $\pm$ 5°	APR. Alex	TITLE: HY2.0弯针WTB		
.XX $\pm$ 0.25	.X.* $\pm$ 3°	CHK. Jack	DWG NO. XY-HY2.0-NAZZ-BL		
.XXX $\pm$ 0.15	.XX.* $\pm$ 1°	DRA. Can	PROJ.	CUSTOMER DRAWING	
SIZE A4	SCALE 1:1	SHEET 1/1	REV. A		



NOTE(注):

- 1.10 SPROCKET HOLE PITCH CUMULATIVE TOLERANCE $\pm 0.2\text{mm}$.
(10片孔距累积公差 $\pm 0.2\text{mm}$.)
- 2.CARRIER CAMBER NOT TO EXCEED 1mm IN 100mm.
(载带拱/弯MAX:1/100mm.)
- 3.ALL DIMENSIONS MEET EIA-481 REQUIREMENTS.
(所有的尺寸要满足协会EIA-481规范.)
- 4.MATERIAL: CLEAR ANTISTATIC PS.
(载带材料: 透明防静电 PS.)
- 5.THICKNESS: $0.40 \pm 0.05\text{mm}$. (载带厚度: $0.40 \pm 0.05\text{mm}$.)
- 6.PACKING LENGTH PER REEL: 8.448 METERS. (每卷包装长度: 8.448米.)
- 7.COMPONENT LOAD PER REEL: 500 PCS. (每卷包装数量: 500R.)
8. 纸带包装以不超过装带线为准, 空余位置用塑料泡沫及保尼龙填充.
9. 纸带分小、中、标准型3种规格型号: 装带为整卷(在下包装量)采用标准型纸带包装, 未达到整卷数量以产品适当采用小型或中型纸带包装.



纸带型号	小型	中型	标准型
Carrier Type	Small Size	Medium	Standard
Height (CM)	7.5	15	32

CKT (2.0mm pitch)	B0	W	F	S
2	6.30	16	7.50	
3	8.30			
4	10.30	24	11.50	
5	12.30			
6	14.30			
7	16.30			
8	18.30	32	14.20±0.10	28.40
9	20.30			
10	22.30			
11	24.30			
12	26.30	44	20.20±0.10	40.40
13	28.30			
14	30.30			
15	32.30			
16	34.30			
17	36.30	56	26.20±0.10	52.40
18	38.30			
19	40.30			
20	42.30			

CKT (2.0mm pitch)	W	PCS/REEL	REEL/CARTON	SUM(PCS)
2	16	400	14	5600
3				
4	24	400	10	4000
5				
6				
7				
8	32	400	8	3200
9				
10				
11				
12	44	400	6	2400
13				
14				
15				
16	56	400	5	2000
17				
18				
19				
20				

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd					
TOLERANCE UNLESS OTHERWISE SPECIFIED							
.X±0.5	X.*± 5°	APR.	Alex	TITLE: HY2.0 0.4mm WTB 载带			
.XX±0.25	.X*± 3°	CHK.	Jack	DWG NO. XY-HY2.0-NA21-BL			
.XXX±0.15	.XX*± 1°	DRA.	Can	PROJ. 		CUSTOMER DRAWING	
				SIZE A4	SCALE 1:1	SHEET 1/1	REV. A