




NOTE:

1.MATERIAL:

- 1.1 INSULATOR: LCP/PA9T UL 94V-0
- 0.1 1.2 CONTACT: BRONZE(T=0.20mm)
- 1.3 SHELL: BRASS/SPCC(T=0.30mm)
2. ELECTRICAL CHARACTERISTICS:
 - 2.1 CONTACT RESISTANCE: 30mΩ MAXIMUM
 - 2.2 CONTACT CURRENT RATING: 1.5A
 - 2.3 DIELECTRIC WITHSTANDING VOLTAGE: 500V R.M.S.
 - 2.4 INSULATION RESISTANCE: 1000 MEGOHMS MIN
 - 2.5 OPERATING TEMPERATURE: -40°C ~ 85°C
3. MECHANICAL CHARACTERISTICS:
 - 3.1 MATING FORCE: 3.57kg MAX
 - 3.2 UNMATED FORCE: 1.02kg MIN
 - 3.3 DURABILITY: MANDATORY: 1500 CYCLES
4. PLATING
 - 4.1 TERMINAL:
 - 50u" MIN NICKEL ALL OVER
 - 100u" MIN Tin ON SOLDER AREA
 - (1~30)u" Au ON CONTACT AREA
 - 4.2 SHELL: 50u" MIN. NICKEL ALL OVER

PIN NUMBER	SIGNAL NAME
1	VBUS
2	D-
3	D+
4	GND
5	StdA_SSRRX
6	StdA_SSRRX
7	GND_DRAIN
8	StdA_SSTX
9	StdA_SSTX
Shell	Shield

MANUFACTURE DWG



东莞市讯普电子科技有限公司
DongGuan XunPu Electronics Co.,Ltd



TITLE: USB3.0 AF 沉板 DIP型 方脚无卷边

PAR	USB-327-ARFW		
DWN	Lucas		
CHKD	Ethan		
APVD	Jacob		
SCALE1:1	UNIT: MM		
SIZE: A4	SHEET: 1F1	REV: A	