


NOTES:

1.MATERIAL:

- 1.1.Housing:HI-TEMP Plastic,UL94V-0,Black;
- 1.2.Terminal:Copper alloy
- 1.3 Shell:Stainless Steel



2.FINISH:

2.1 Terminal:


- Au Plated on the contact area, Matte tin plated on the solder tails underplated over nickel;
- 2.2 NAIL: Plated Au On The Solder Area.

3. Electrical Performance:

- 3.1 Contact Resistance:50mΩ Max
 - 3.2 Dielectric Withstanding Voltage:350V AC rms for 1 minut
 - 3.3 Insulation Resistance:1000 MΩ Min
4. Mechanical Performance:
- 4.1 Durability:3000 cycles;
 - 4.2 Normal force: 20gf/PIN Min;





PUSH THE SHELL



C1	C1:VCC
C2	C2:RST
C3	C3:CLK
C4	C4:RESERVED
C5	C5:GND
C6	C6:VPP
C7	C7:I/O
C8	C8:RESERVED

SIM CARD CIRCUIT



RECOMMENDED P.C.BOARD LAYOUT (TOP VIEW)
TOLERANCES UNLESS OTHERWISE SPEC.±0.05

▨ : PAD AREA □ : KEEP OUT AREA

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd		
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE:1.8H 6PIN SIM CARD HINGE TYPE FOR CUSTOMER	
			PAR	SIM-106A-ARP6
DECIMALS:	ANGLES:		DWN	
X.:±0.20	X'':±2°		CHKD	
.X:±0.15	.X':±1°		APVD	
.XX:±0.10	.XX':±0.5°	SCALE:1:1	UNIT:MM	
CUSTOMER COPY		SIZE:A4	SHEET:1F1	REV:A