








NOTE:

1.MATERIAL:

- 1.1 INSULATOR:LCP UL 94V-0
- 1.2 CONTACT:COPPER(5PIN:T=0.20/4PIN:T=0.25)
- 1.3 SHELL:BRASS(T=0.30/T=0.20)

2.ELECTRICAL CHARACTERISTICS:

- 2.1 CONTACT RESISTANCE:30mΩ MAXIMUM
- 2.2 CONTACT CURRENT RATING:1.5A
- 2.3 DIELECTRIC WITHSTANDING VOLTAGE:100V R.M.S.
- 2.4 INSULATION RESISTANCE 100 MEGOHMS MIN
- 2.5 OPERATING TEMPERATURE:-40°C ~ 85°C

3.MECHANICAL CHARACTERISTICS:

- 3.1 MATING FORCE:3.57kg MAX
- 3.2 UNMATED FORCE:1.02kg MIN INITIAL/0.82kg MIN AFTER TEST.
- 3.3 DURABILITY:1,500 CYCLES MIN

4.PLATING

- 4.1 TERMINAL:50u" MIN NICKEL ALL OVER 80u"MIN Tin ON SOLDER AREA(1~30)u"Au ON CONTACT AREA
- 4.2 SHELL:NICEL PLATED

PIN NUMBER	SIGNAL NAME
1	VBUS
2	D-
3	D+
4	GND
5	StdA_SSTX-
6	StdA_SSTX+
7	GND_DRAIN
8	StdA_SSRX-
9	StdA_SSRX+
Shell	Shield

MANUFACTURE DWG

UNLESS OTHERWISE SPECIFIED TOLERANCES

DECIMALS:

X.:±0.50

X.X:±0.30

X.XX:±0.20

ANGLES:

X'±2°

X.X'±1°

X.XX'±0.5°

东莞市讯普电子科技有限公司
DongGuan XunPu Electronics Co.,LtdTITLE:USB3.0 BF90度弯脚插板
成品图(H=12.4)

PAR	USB-B304-ARDW
DWN	Lucas
CHKD	Ethan
APVD	Jacob
SCALE:1:1	UNIT:MM
SIZE:A4	SHEET:1F1
CUSTOMER COPY	REV:A