






SPECIFICATION:

1.MATERIAL:

HOUSING: LCP UL 94V-0

COLOR:BLACK

CONTACT: PHOSPHOR BRONZE C5191R-H,T=0.25mm

PEG:C2680R-H,T=0.50mm

2.FINISH:






CONTACT:1u"/3u"/5u"/15u" GOLDPLATING ON CONTACT AREA

100u" TIN PLATING ON SOLDERTAILS

30u" NICKEL UNDERPLATING OVER ALL

PEG: 100u" TIN PLATING ON SOLDERTAILS

30u" NICKEL UNDERPLATING OVER ALL

RECOMMENDED PCB LAYOUT
PCB TOLERANCE:±0.05

环保要求		产品必须符合ROHS要求		
3	Peg	Brass C2680R-H		Tin/Ni Plated
2	Terminal	Pho.Bronze C5191R-H		Gold/Tin Plated
1	Housing	High Temp	Black	UL 94V-0
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK
MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd		
UNLESS OTHERWISE SPECIFIED TOLERANCES		 TITLE:SATA 7+15P 母座 DIP 180° 双排双鱼叉加长型针长2.7		
DECIMALS:		PAR	SATA-13M-22AZZ-Z27	
ANGLES:		DWN	Lucas	
X.:±0.30	X':±5°	CHKD	Ethan	
X.X:±0.20	X.X':±3°	APVD	Jacob	
X.XX:±0.10	X.XX':±2°	SCALE:1:1	UNIT:MM	⌀
CUSTOMER COPY		SIZE:A4	SHEET:1F1	REV:A