









Recommended P.C.B Layout

TECHNICAL CHARACTERISTICS
MATERIAL
INSULATOR: PA6/66
FLAMMABILITY RATING: UL94V0
COLOR:
CONTACT / PLATING: COPPER ALLOY / Ni+Sn
ENVIRONMENTAL
OPERATING TEMPERATURE: -30°C UP TO +120°C
COMPLIANCE: LEAD FREE AND ROHS
ELECTRICAL VDE
CURRENT RATING: 6.3A
WORKING VOLTAGE: 250VAC
WITHSTANDING VOLTAGE: 1.5KV
RATED POWER ACCEPTANCE: 1.6W
PROTECTION CLASS: I o II
CONTACT RESISTANCE: 5/10 m
MECHANICAL
FUSE-LINK: 5x20 mm
PROTECTION RATE: IP00
SHOCKSAFE CATEGORY: PC1

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			

APPROVALS		DATE		DEALON 德之隆® ELECTRONICS CO.,LTD				
DRAWN	G.M.Chen	2014/11/26		TITLE: FUSE HOLDER				
CHECKED								
APPROVALS				PART NO. BX5020-W				
TOLERANCES ARE		30~0.15 10~0.30 5~10 ~5	±0.30 ±0.20 ±0.15 ±0.10	ANGLE		UNIT: mm	SCALE: 1:1	SHEET 1 OF 1
						DRAWING NO.		PROJ. 