





RoHS



PCB Layout recommended



Circuit Diagram



TOTAL HEIGHT	
Code	H
033	3.3
035	3.5
038	3.8
043	4.3

Product No. : TS-087C-□□□□

型号:

产品高度 (H) :

033=3.3mm

035=3.5mm

038=3.8mm

: 包装方式

-P=编带 (非编带, 不启用)

: 弹片



D2=SUS/1PCS

D4=SUS/2PCS

操作力度:

180=180gf±50gf

250=250gf±50gf



Ⓔ	Terminal		2	Phosphor Bronze	Silvering
Ⓓ	Contact		1	SUS	Silver covered
Ⓒ	Base		1	LCP	White
Ⓑ	Cover		1	Brass	Ag plated
Ⓐ	Knob		1	LCP	Black
NO.	Name	Number	Qty	Materil	Remarks

ZHONGDI®

Zhongdi Electronic Technology Co., Ltd

design	date	name	TACT SWITCHS
Review	date	model	TS-087C-□□-D□
Approved	date		

Drawing number:

Proportion 1:1 unit mm gage number A4

modify Review Approved

angle	±2°
10~30	±0.30
5~10	±0.20
~ 5	±0.10

Tolerance not specified

项 目 Item	技术参数 Technical Parameter	标 准 Standard
电气性能 Electrical Properties	额定电流 Rated Current:	50mA
	额定电压 Rated voltage:	DC 12V
	接触电阻 Contact resistance:	≤100mΩ
	绝缘电阻 Insulation Resistance:	DC 250V 1 min ≥100MΩ
机械 性能 Mechanical Properties	耐压强度 Compressive strength:	AC 250V 50Hz/1 min
	机械寿命 Mechanical life:	30,000 cycles Min
环境性能 Environmental	操作行程 Operation Stroke:	0.20±0.10mm
	工作温度 Operation temperature:	-25℃~ +75℃
可靠性特性 Reliability Characteristics	使用湿度 Use humidity:	≤85% RH
	回流焊 Reflow Soldering:	≤260℃ 时间 Time 3s
	波峰焊 Wave soldering:	
应用领域 Application area	手工焊 Manual welding:	≥260℃ 时间 Time 3s
	影音产品、电子玩具、数码产品、通讯产品、安防产品等. Audiovisual products, electronic toys, digital products, communication products, security products, etc	



绝缘电阻测量仪



直流低电阻测试仪




耐电压测试仪



回流焊机



二次元测量仪



高精密寿命测试仪



盐雾测试仪



按键荷重曲线仪

ZHONGDI® 众迪					Zhongdi Electronic Technology Co., Ltd				
design		date		name	TACT SWITCHS				
Review		date			TS-087C-□□-D□				
Approved		date							
number:				model					

modify	Review	Approved	Tolerance not specified	Proportion	1:1	unit	mm	gape number	A4
--------	--------	----------	-------------------------	------------	-----	------	----	-------------	----