



Multilayer Low Pass Filter

◆ Dimensions(Unit:mm)





L	W	T	a	b	c	d	e	f
1.6±0.1	0.8±0.1	0.35±0.05	0.225±0.05	0.4±0.1	0.3±0.05	0.65±0.1	0.21±0.05	0.22±0.05

◆ Recommended Land Pattern



◆ Electrical Characteristics(Temperature=25℃)




Terminal Configuration			
NO.	Terminal Name	NO.	Terminal Name
(1)	In	(2)	GND
(3)	Out	(4)	GND

◆ Electrical Characteristics

Item	Frequency Range (MHz)	Min	Max
Insertion Loss (dB)	2400~2500	-	0.48
Return Loss (dB)	2400~2500	12	-
Attenuation (dB)	4800~5000	35	-
	7200~7500	35	-
Characteristic impedance		50Ω	

◆ General Specification

- 1:Operating Temp:-40~85°C
 2:Resistance to soldering heat:
 Solder temp: 260°C
 Dip time:10 sec max



◆ Packaging:4000PCS/Reel