







OFF POSITION
6 POS AVAIL



RECOMMENDED PCB LAYOUT



D V 7 S A -06 F - 01

Dip Switch

Appearance
V=Vertical

Pin Pitch
7=1.27 Pitch

PCB Form
S=SMT

G-Switch Type
A= A Type

Extended Encoding
01=Stick Mylar
02=Not have Mylar

Position
N=ON
F=OFF

Part No.
01=01Pin 02=02Pin
03=03Pin 04=04Pin
05=05Pin 06=06Pin
07=07Pin 08=08Pin
09=09Pin 10=10Pin
11=11Pin 12=12Pin

G-Switch Specification:

- Operating temperature range: -40°C ~ +85°C
- Rating: 50mA. 12V DC
- Insulation resistance: 100MΩ min. 100V DC
- Dielectric strength: 250V AC for 1 min
- Contact resistance: 100m Ω max.
- Travel: 0.7±0.1mm
- Operating Life: 1,000 cycles

1	MYLAR	PI	YELLOW
2	COVER	HTN FR52G30	BLACK
3	ACTUATOR	LCP-E6006L	TRUE QUALITIES
4	TETMINAL CONTACT	COPPER ALLOY(C5240)	CONDUCTION POSITION GOLD PLATING
5	BASE	HTN FR52G30	BLACK
6	TERMINAL	COPPER ALLOY(C5191)	CONDUCTION POSITION GOLD PLATING
NO.	PART NAME	MATERIAL	REMARK



RoHS
Compliant
EU RoHS Standards



SCALE: 1:1 UNIT: mm
SIZE: A4

Unless otherwise
General Tolerance:
X ±0.30
X.x ±0.20
X.xx ±0.15
X.xxx ±0.10
Angles ±3°

Title: Horizontal 1.27 Pitch Dip Switch
SMT 6Pin Off Stick Mylar

Molde Code: DV7SA-06F-01

DRAWN	CHECKED	APPROVED	DATE
Xia	Chen	Chen	2023.04.24

品赞科技®
b-Switch

REV: A0 SHEET: 1/1