










SECTION A-A
AFTER MATING



PCB REFERENCE DIAGRAM
TOLERANCE:±0.05

G-Switch USB-C Specification:

- 1.Current rated: 5A on vbus/1.25A on vconn/0.25A on other
- 2.Withstanding voltage: 100V AC/minute
- 3.Contact resistance: 40mΩ Max
- 4.Insulation resistance: 100MΩ Min
- 5.Operating temperature: -40°C ~ +85°C
- 6.Mating force: 5N~20N
- 7.Unmating force: 8N~20N,after durability test: 6N~20N
- 8.Durability cycle:10,000 cycles

A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12
GND			VBUS	CC1	D+	D-	SBU1	VBUS			GND
First			First	Second	Second	Second	Second	First			First

B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1
GND			VBUS	SBU2	D-	D+	CC2	VBUS			GND
First			First	Second	Second	Second	Second	First			First

NO.	PARTS	MATERIAL	REMARKS
1	SHELL	SUS316	NI PLATED
2	GND PLATE	SUS304	---
3	MID PLATE	SUS301	NI PLATED
4	HOUSING	LCP+30%G.F	BLACK UL 94V-0
5	TERMINALS	C7025	Au PLATED ON CONTACT AREA G/F PLATED ON SOLDER AREA

Molde Code	Contact Plated
GT-USB-7055J	G/F PLATED
GT-USB-7055J-03	Au3u* PLATED



SCALE: 1:1	UNIT: mm	Title: Vertical Type-C 16P Female SMT H=10.5mm			
SIZE: A4		Molde Code: GT-USB-7055J			
Unless otherwise General Tolerance: X. ±0.40 X.x ±0.30 X.xx ±0.20 X.xxx ±0.10 X* ±5°		DRAWN	CHECKED	APPROVED	DATE
		Xia	Chen	Chen	2025.05.28



REV: A1	SHEET: 1/1
---------	------------