


客户图

NO.	ECN NO.	DESCRIPTION	DATE



技术要求:

1. 材料:黄铜C3604.
2. 切断点最大不超过0.03mm, 产品注意不能抛光;
3. 表面处理: 镀金3u', 镍底50-100u'

深圳市鑫探技术有限公司

[HTTP://WWW.XYZPOGOPIN.COM](http://www.xyzpogopin.com)

TEL:0755-28773277 FAX:0755-28891353



SCALE:	N/A	UNIT	mm
SHEET:	1 of 1	PROJECTION	
DATE:	2025.2.19	VER.	0

THE UNMARKED TOLERANCE ARE AS BELOW :

LENGTH		ANGLE	
X.XX	±0.05mm	X.XX	±0.50°
X.X	±0.10mm	X.X	±1.00°
X.	±0.20mm	X.	±2.00°

DESIGNED BY:		DWG. NO.	YZT1164-15018-G3
CHECKED BY:		TITLE:	车件
APPROVED BY:			