











This document is the property of Xinshengyue Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Xinshengyue Corporation without its prior concert&that no right is granted to disclose or to use any information in this document.

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN
A	ECN NO.	INITIAL RELEASED	2026.08.11	JANUS

RoHS & HF
Compliant



SECTION:A-A




MATED CONDITION (REF.)

TOLERANCE		NAME(INTENDED USE) CUSTOMER DRAWING	XSUA® 深圳市新升跃精密电子有限公司 SHENZHEN XINSHENGYUE PRECISION ELECTRONICS CO., LTD			
X.X	±0.30	X.* ±10°	PART NO.	TITLE: TYPEC母座24PIN长8.2MM 板上脚长0.73 (CH=1.6) 40G		
.XX	±0.20	.X.* ± 8°	101015-211030			
.XXX	±0.10	.XX.* ± 5°	DESIGN: JANUS	DRAWG NO.		
UNIT	mm			C-101015		
MATERIAL	---	CHED: JANUS				
FINISH	---	APPD: ARAY				
				SCALE	SHEET	REV.
				1:1	1/3	A

This document is the property of Xinshengyue Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Xinshengyue Corporation without its prior consent&that no right is granted to disclose or to use any information in this document.

RoHS & HF
Compliant



SCALE 2:1
RECOMMENDED PCB LAYOUT(TOP VIEW)
Thickness 1.0mm (TOLERANCE=±0.05mm)

P/N: 101015-211030

- CONTACT FUNCTIONAL AREA PLATED
03: Au 3u"
- CONTACT SOLDER AREA PLATED
1: Au G/F
- PACKAGING
1: REEL PACKAGING

- NOTE:
- 1.MATERIAL SPECIFICATION:
 - 1.HOUSING:LCP(E6808),UL94 V-0.
 - 2.TERMINAL:COPPER ALLOY(C18150)
 - 3.MID PLATE: STAINLESS STEEL(SUS301)
 - 4.OUT SHELL: STAINLESS STEEL(SUS304)
 - 5.INNER SHELL: STAINLESS STEEL(SUS304)
 - 2.PLATING SPECIFICATION:
 - 2-1.CONTACTS:
 - Ni 50u" MIN. UNDER PLATED OVER ALL.
 - Au 3u" PLATED ON CONTACT AREA
 - PLATING GOLD 1u" ON SOLDER AREA
 - 2-2.OUT SHELL&INNER SHELL:
 - Ni 50u" MIN. UNDER PLATED OVER ALL.
 - 2-3.MID PLATE:
 - Ni 50u" MIN. UNDER PLATED OVER ALL.
 - 3.MECHANICAL PERFORMANCE,
 - 3-1.INSERTION FORCE: 0.5~2.0kgf.
 - 3-2.REMOVAL FORCE: 0.8kgf~2.0kgf.(INITIAL)
0.6kgf~2.0kgf.(AFTER DURABILITY TEST)
 - 3-3.DURABILITY: 10000 CYCLES.
 - 4.ELECTRICAL PERFORMANCE,
 - 4-1. VOLTAGE RATING:48 V DC/AC (RMS. MAX)
CURRENT RATING:5 AMPS. FOR TOTAL VBUS/GND PINS;
1.25AMPS FOR CC PIN,0.25AMPS. FOR ALL OTHER CONTACT.
 - 4-2. LLCR:
 - VBUS & GND PINS AND OTHER PINS: 40mΩ/PIN MAX.
 - LLCR MAX. CHANGE OF ALL PINS: 10mΩ.
 - 4-3.INSULATION RESISTANCE: 100MΩ MIN
 - 4-4.DIELECTRIC WITHSTAND VOLTAGE,AC 100V FOR 1 MINUTE.
 - 5. ENVIRONMENTAL PERFORMANCE:
OPERATING TEMPERATURE: -40°C~+105°C.
 - 6.IR REFLOW:
THE PEAK TEMPERATURE ON THE BOARD SHALL
BE MAINTAINED FOR 10 SECONDS AT 260°C.


USB TYPE-C PIN ASSIGNMENTS

A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12
GND	TXp1	TXn1	VBUS	CC1	D+	D-	SBU1	VBUS	RXn2	RXp2	GND
GND	RXp1	RXn1	VBUS	SBU2	D-	D+	CC2	VBUS	TXn2	TXp2	GND
B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1




TOLERANCE		NAME(INTENDED USE) CUSTOMER DRAWING	XSUA® 深圳市新升跃精密电子有限公司 SHENZHEN XINSHENGYUE PRECISION ELECTRONICS CO.,LTD			
X.X ±0.30	X.* ±10°	PART NO.	TITLE: TYPEC母座24PIN长8.2MM 板上脚长0.73 (CH=1.6) 40G			
.XX ±0.20	.X.* ± 8°	101015-211030				
.XXX ±0.10	.XX.* ± 5°	DESIGN: JANUS	DRAWG NO. C-101015			
UNIT	mm					
MATERIAL	---	CHED: JANUS	 SCALE SHEET REV.			
FINISH	---	APPD: ARAY				

This document is the property of Xinshengyue Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Xinshengyue Corporation without its prior concert&that no right is granted to disclose or to use any information in this document.

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN
A	ECN NO.	INITIAL RELEASED	2026.08.11	JANUS



SEE DETAIL X



			REEL		CARTON		
		CONNECTOR (PCS)	900		9000		
TOLERANCE		NAME(INTENDED USE) CUSTOMER DRAWING		XSUA® 深圳市新升跃精密电子有限公司 SHENZHEN XINSHENGYUE PRECISION ELECTRONICS CO., LTD			
X.X ±0.30	X* ±10'	PART NO.					
.XX ±0.20	.X* ± 8'	101015-211030		TITLE: TYPEC母座24PIN长8.2MM 板上脚长0.73 (CH=1.6) 40G			
.XXX ±0.10	.XX* ± 5'	DESIGN: JANUS		DRAWG NO. C-101015			
UNIT	mm	CHED: JANUS					
MATERIAL	---	APPD: ARAY					
FINISH	---			SCALE	SHEET	REV.	
				1:1	1/3	A	