

MDPX24601516D21

Diplexer For 1550-1610MHz / 2400-6000MHz

MECSINE 兆讯

Multilayer Diplexer

For 1550-1610MHz / 2400-6000MHz

MDPX24601516D21

2 x 1.25mm [EIA 0805]

All Use For RF & Microwave

Shenzhen Megsine technology co., ltd www.megsine.com sales@megsine.com may contain us for future information
Feb. 03, 2024


MDPX24601516D21

Diplexer For 1550-1610MHz / 2400-6000MHz

MECSINE 兆讯

APPLICATIONS

- 1, Low Insertion Loss
- 2, Small size in 0805
- 3, Excellent high-power capacity up to 2W
- 4, RoHS compliance (Pb-Free)
- 5, AEC-Q200 qualified



DESCRIPTION

Megsine' MDPX24601516D21 is a MiPD diplexer with a low passband from 1550 to 1610 MHz and a high passband from 2400 to 6000 MHz, optimized for diplexing low band and high band signals. The MDPX24601516D21 is ideal for low insertion loss and wide band application. It is suitable used in smart phone, 5G module and other IOT modules. It is constructed from organic material which possess excellent electrical and mechanical stability. All components are 100% RF tested.

MAXIMUM RATINGS

Characteristic	Ratings	Units
RF Power (in BW)	33	dBm
Operating Temperature Range	-40~+105	°C
Storage Temperature Range	-40~+125	°C
Moisture Sensitivity Levels	3	MSL
ESD Level Human Body Model	8000	V

ELECTRICAL CHARACTERISTICS

Low-Band

Item	Frequency Range (MHz)	Min.	Typ.	Max.
Insertion Loss (dB)	1550 to 1610	-	0.85	1
Return Loss (dB)	1550 to 1610	10	16	-
Attenuation (dB)	2400 to 2500	14	23	-
	4900 to 6000	15	21	-
Characteristics Impedance (Ω)		50 (Nominal)		

- Ta: +25±5°C

High-Band

Item	Frequency Range (MHz)	Min.	Typ.	Max.
Insertion Loss (dB)	2400 to 2500	-	0.85	1.45
	4900 to 6000		0.75	1.25
Return Loss (dB)	2400 to 2500	10	15	-
	4900 to 6000	10	20	
Attenuation (dB)	1550 to 1610	12	18	-
Characteristics Impedance (Ω)		50 (Nominal)		

- Ta: +25±5°C

All Use For RF & Microwave

MDPX24601516D21

Diplexer For 1550-1610MHz / 2400-6000MHz


MECSINE 兆讯

Common

Item	Frequency Range (MHz)	Min.	Typ.	Max.
Isolation (dB)	1550 to 1610	12	18	-
	2400 to 2500	14	25	-
	4900 to 6000	15	22	-
Characteristics Impedance (Ω)		50 (Nominal)		

- Ta: +25±5°C


SHAPES AND DIMENSIONS




Unit: mm Tolerance:±0.1

FREQUENCY CHARACTERISTICS

Low-Band Insertion Loss



High-Band Insertion Loss




All Use For RF & Microwave

MDPX24601516D21


Diplexer For 1550-1610MHz / 2400-6000MHz

MECSINE 兆讯


Low-Band Attenuation




High-Band Attenuation



Common Return Loss



Common Isolation




All Use For RF & Microwave

MDPX24601516D21


Diplexer For 1550-1610MHz / 2400-6000MHz

MECSINE

RECOMMENDED LAND PATTERN AND EVALUATION BOARD



PACKAGING AND ORDERING INFORMATION



Device	Package	Reel	Shipping
MDPX24601516D21	2*1.25mm	7"	3000 Reel

Revision	Description	Date
Rev0	Preliminary	2026/07/20

All Use For RF & Microwave

Shenzhen Megsine technology co., ltd www.megsine.com sales@megsine.com may contain us for future information
Feb. 03, 2024