


客户图



Note:

1: Material(材料):

Barrel: Brass C3604 (针管: 黄铜 C3604)

Plunger: Brass C3604 (针头: 黄铜 C3604)

Spring: SUS304 (弹簧: SUS304)

2: Plating(电镀):

Barrel: 3u' Au over 50~80u' Ni(针管: 镀金3u', 镍底50~80u'.)

Plunger: 3u' Au over 50~80u' Ni (针头: 镀金3u', 镍底50~80u'.)

Spring: No plated (弹簧: 不电镀)

3: Electrical(电气特性):

Rated Current & Voltage: DC 12V;2A (额定电压&电流: 直流12,2A)

Contact Resistance: 50 mohm Max. at working height.

接触电阻: 最大50毫欧 (在工作高度状态下)

4: Mechanical(机械性能):

Force: 40g±20% at working height. (40g±20% 在工作高度)。

Durability: 10.000 cycles(min) (寿命: 10000次)

5: WorkTemperture(工作环境):

Withstanding Higt Temperature: 280℃

Operational Temperature: - 40℃~ +85℃

深圳市鑫探技术有限公司



TEL:0755-28773277 FAX:0755-28891353

SCALE:

N/A

UNIT

mm

SHEET:

1 of 1

PROJECTION



DATE:

2016.09.22

VER.

D.1

THE UNMARKED TOLERANCE ARE AS BELOW:

LENGTH

ANGLE

X.XX

±0.05mm

X.XX

±0.50°

X.X

±0.10mm

X.X

±1.00°

X.

±0.20mm

X.

±2.00°

DESIGNED BY:

DWG. NO.

YZP0364-18108-01

CHECKED BY:

TITLE:

成品图

APPROVED BY: