



客户图



技术要求:

1. 材料:黄铜C3604.
2. 不允许有批锋, 毛刺; 切断点最大不超过0.03mm.
3. 表面处理: 镀金3u', 镍底50-80u';

深圳市鑫探技术有限公司

HTTP://WWW.XYZPOGOPIN.COM

TEL:0755-28773277 FAX:0755-28891353



SCALE:	N/A	UNIT	mm
SHEET:	1 of 1	PROJECTION	
DATE:	2024.12.16	VER.	0

THE UNMARKED TOLERANCE ARE AS BELOW :			
LENGTH		ANGLE	
X.XX	±0.05mm	X.XX	±0.50°
X.X	±0.10mm	X.X	±1.00°
X.	±0.20mm	X.	±2.00°

DESIGNED BY:		DWG. NO.	YZT1151-25057-G3
CHECKED BY:		TITLE:	车件
APPROVED BY:			