









RoHS Compliant





MEASURE POINT: QUADRANT POINT (QP) TANGENCY POINT (TP) INTERSECTION POINT (IP)				联晟欣连接器 (深圳) 有限公司 Lianshengxin Connector (Shenzhen) Co., Ltd			
UNLESS OTHERWISE SPECIFIED, TOLERANCE:				DESIGN	Andy	DATE	2014.12.24
X. ±0.25				CHECKED		DATE	
X.x ±0.20				APPROVED		DATE	
X.xx ±0.15				PART NO: LCK367BA0050A			
ANGULAR ±3°				DRAWING NO: 102022802			
				REV: 04	SCALE: 1:1	UNIT: mm	
				SIZE: A4	SHEET: 1/1		

TITLE:
充电弹片 L2.97×1.34×H3.67
charging contact spring

RoHS Compliant

耳机插入示意图(仅供参考)



3D VIEW

NOTES:

1:MATERIAL:

1-1:STAINLESS STEEL THICKNE=0.08±0.03mm

2:FINISH:

2-1:REFER TO THE SPECIFICATION DESCRIPTION TABLE.

2-2:DIMENSIONS OF PCB PAD STENCIL

ARE FOR REFERENCE ONLY,
CUSTOMER CAN MODIFY IT BY THEIR OWN.

3:PRODUCT SPECIFICATIONS:

3-1:RATED CURRENT:1.5A/MAX

3-2:VOLTAGE RATING:5.0V/AC/DC/MAX

3-3:CONTACT RESISTANCE:50mΩ/MAX

3-5:OPERATING TEMPERATURE:-40°C~85°C

3-6:NORMAL FORCE OF PRESS@0.50:18gf±8gf.

3-7:DURABILITY:10,000 CYCLES.


4:SALT SPRAY:48 HOURS(JUDGED BY ALL OUTSIDE AREA)

5:PACKING SPECIFICATION:REEL&TARE



6:DIMENSIONS MARKED ▣,CPK>1.33

7:ALL DIMENSIONS MARKED ▼ MUST BE CONTROLLED BY QC;

8:COMPLIANT TO RoHS&LEAD FREE



耳机插入力曲线图(仅供参考)



RECOMMENDED PCB LAYOUT
TOLERANCE±0.05(焊盘推荐图)
(FOR REFERENCE ONLY)

MEASURE POINT:		 联晟欣连接器（深圳）有限公司 Lianshengxin Connector (Shenzhen) Co., Ltd				
QUADRANT POINT	ⓀⓅ					
TANGENCY POINT	ⓉⓅ					
INTERSECTION POINT	ⓂⓅ					
UNLESS OTHERWISE SPECIFIED, TOLERANCE:		DESIGN	Andy	DATE	2014.12.24	TITLE:
X.	±0.25	CHECKED		DATE		充电弹片L2.97×1.34×H3.67 charging contact spring
X.x	±0.20	APPROVED		DATE		
X.xx	±0.15	PART NO: LCK367BA0050A				
ANGULAR	±3°	DRAWING NO: 102022802				REV: 04
						SCALE: 1:1
						UNIT: mm
						SIZE: A4
						SHEET: 1/1
						