



产品承认书

SPECIFICATION FOR APPROVAL

客户名称:
CUSTOMER

我司料号:
OUR PART NO.

XRSQ1915-15mH-V-1013

我司品名:
OUR PART NAME

SQ flat wire inductor

送样日期:
DATE SAMPLES

数量:
QUANTITY

制造确认 MANUFACTURER APPROVE

拟制 DRAWN	审核 CHECKED	确认 APPROVED
Hu Fangting	RaoPing	ZhongCuilan

客户确认 CUSTOMER APPROVE

客户名称 CUSTOMER NAME:

客户料号 CUSTOMER P/N:

规格型号 DESCRIPTION:

SQ1915-15mH Vertical with 10*13 pin pitch
0.3*1.5mm

检查结果: ☐ 合格 ☐ 不合格

签名及盖章:

INSPECT RESULT ACCEPT REJECT

SIGNATURE AND STAMP

说明 REMARK:

如对本承认书内容有异议请提出或标记发送至我司，本承认书在未收到异议回复时于本承认书提供一周后生效。

If you have any objection to the contents of this acknowledgment, please raise it or send the mark to us.
The acknowledgment will become effective one week after the acknowledgment is provided in the absence of any objection.

东莞市祥如电子有限公司

DONGGUAN XIANGRU ELECTRONICS CO.,LTD

Tel: 0769-86346548 Fax: 0769-86346358

Email: dgxiangru@126.com



产品承认书
SPECIFICATION FOR APPROVAL

CUSTOMER _____

CUSTOMER'S PART NO _____

VER _____ A

DESCRIPTION SQ1915-15mH Vertical with 10*13 pin pitch
0.3*1.5mm

OUR DRAWING NO XRSQ1915-15mH-V-1013

A REVISION HISTORY

DATE OF	REVISED PROJECT	EDITION	NOTE
2025/9/10	NEEW VERSION	A	

Page2/7

PPROVED BY	CHECKED BY	PREPARED BY	UNIT	mm
Li Zhengxiong	TangWen	Hu Fangting	DATE	2025/9/10
			REV NO.	A

产品承认书


SPECIFICATION FOR APPROVAL

CUSTOMER _____


CUSTOMER'S PART NO _____ VER _____ A

DESCRIPTION SQ1915-15mH Vertical with 10*13 pin pitch 0.3*1.5mm OUR DRAWING NO XRSQ1915-15mH-V-1013


1. APPEARANCE & DIMENSION (UNIT: mm):




正视图
Frontal View



侧视图
Side View



底视图
Bottom View



绕线示意图
Winding Diagram

A	B	C	D	E	F	G	H	I
23.0MAX	23.5MAX	15.0MAX	3.5±0.5	10.0±0.5	12.8±0.5	0.8±0.1	20.0±0.5	14.0±0.5

NOTE:

- 产品共模绕制。
Product common mode winding
- 产品需含浸凡立水固定。
The product needs to be impregnated with varnish for fixing
- 焊点不可高于底座支点。
The solder joints must not be higher than the base support points.

PPROVED BY	CHECKED BY	PREPARED BY	UNIT	mm
Li Zhengxiong	TangWen	Hu Fangting	DATE	2025/9/10
			REV NO.	A



产品承认书
SPECIFICATION FOR APPROVAL

CUSTOMER _____


CUSTOMER'S PART NO _____

VER _____ A


DESCRIPTION SQ1915-15mH Vertical with 10*13 pin pitch
0.3*1.5mm

OUR DRAWING NO XRSQ1915-15mH-V-1013

2. SCHEMATIC:



3. WINDING SEQUENCE:



4. WINDING TABLE

ORDER	WIRE SIZE	START	END	TURNS	LAYER	INSULATION	
N1	0.3*1.5mm UEWH FlstWire	1	2	25TS (REF)	CLOSE		
N2	0.3*1.5mm UEWH FlstWire	4	3	25TS (REF)	CLOSE		

Page4/7

PPROVED BY	CHECKED BY	PREPARED BY	UNIT	mm
Li Zhengxiong	TangWen	Hu Fangting	DATE	2025/9/10
			REV NO.	A



产品承认书
SPECIFICATION FOR APPROVAL

CUSTOMER _____

CUSTOMER'S PART NO _____

VER _____

A

DESCRIPTION SQ1915-15mH Vertical with 10*13 pin pitch
0.3*1.5mm

OUR DRAWING NO XRSQ1915-15mH-V-1013

5.ELECTRICAL CHARACTERISTICS:

TEST CONDITION:		TEMPERATURE AT: 25°C±5°C WORKING TEMPERATURE: -25°C/+125°C STORAGE TEMPERATURE: -25°C/+40°C HUMIDITY: AT45-80% RH	
TEST INSTRUMENT	CHENHWA/1062	CHENHWA/1062	CHENHWA/502A
ITEM TERMINAL	INDUCTANCE 1KHz,0.25Vrms 25°	DIFFERENCE INDUCTANCE 1KHz,0.25V	DC.RESISTANCE AT 25°C
1-2	15mH MIN	0.3mH Max	40mΩMAX
4-3	15mH MIN	0.3mH Max	40mΩMAX
TEST INSTRUMENT	E-SUN 19053	E-SUN/19053	
ITEM TERMINAL	HI-POT TEST AC50/60Hz, 5mA, 3sec	INSULATION RESISTANCE.DC 500V	
COIL-COIL	1500V	100M Ω MIN	
COIL-CORE	1000V	100M Ω MIN	
Idc		3.6A	

Page5/7

PPROVED BY	CHECKED BY	PREPARED BY	UNIT	mm
Li Zhengxiong	TangWen	Hu Fangting	DATE	2025/9/10
			REV NO.	A



注意事项 Matters needing attention

CUSTOMER _____

CUSTOMER'S PART NO _____

VER _____ A

DESCRIPTION SQ1915-15mH Vertical with 10*13 pin pitch
0.3*1.5mm

OUR DRAWING XRSQ1915-15mH-V-
NO 1013

6.MATERIAL LIST:

N0	ITEM	MATERIAL	CLASS	UL NO	MANUFACTURER	OPT.
1	CORE	SQ1915 12K			ACMEElectronics(Guangzhou)Co;Ltd	√
		SQ1915 12K			SHANGDONG hengrui magnet technology CO.,LTD	√
		SQ1915 12K			DongGuan City JiuXin Magnetic Material Co.,Ltd	√
		SQ1915 12K			TengZhou MingJi Magnetism Industry Co., Ltd	√
2	BOBBIN	T375HF	150℃	E59481	CHANG CHUN PLASTICS CO LTD	√
3	WIRE	@* FIWx180	180℃	E234867	SUNTEK HOLDINGS LIMITED	√
		@* UEW180	180℃	E504985	Guangdong Lizewire Electric Technology Co Ltd	√
4	VARNIS H	E962	130℃	E335405	ZHUHAI CHANGXIAN NEW MATERIALSTECHNOLOGY CO LTD	√
5	tin	wuxi conditions /Sn99.9			Dongguan City Thousand Island METAL FoilCO LTD	√

Page6/7

PPROVED BY	CHECKED BY	PREPARED BY	UNIT	mm
Li Zhengxiong	TangWen	Hu Fangting	DATE	2025/9/10
			REV NO.	A



产品承认书
SPECIFICATION FOR APPROVAL

CUSTOMER

CUSTOMER'S PART NO

VER

A

DESCRIPTION

SQ1915-15mH Vertical with 10*13 pin pitch
0.3*1.5mm

OUR DRAWING NO

XRSQ1915-15mH-V-1013

7.THE INSPECTION REPORT

ITEM	TEXT SPEC.	1	2	3	4	5
L 值(1-2)	15mH MIN 1KHZ 0.25V 25°	19.4	20.05	18.9	20.4	17.6
L 值(4-3)	15mH MIN 1KHZ 0.25V 25°	19.4	20.05	18.9	20.4	17.6
DCR 值(1-2)	40mΩMAX AT 25℃	OK	OK	OK	OK	OK
DCR 值(4-3)	40mΩMAX AT 25℃	OK	OK	OK	OK	OK
HI-POT AC50/60Hz 5mA 3sec						
	COIL-COIL:1500V	OK	OK	OK	OK	OK
	COLI-CORE:1000V	OK	OK	OK	OK	OK

TEST EQUIPMENT

INDUCTANCE

DC.R

CH-3250: ()

HI-POT

CH-1062: (√)

E-SUN-19053 (√) CH-502BC (√)

CH-101: ()

Page4/7

PPROVED BY	CHECKED BY	PREPARED BY	UNIT	mm
Li Zhengxiong	TangWen	Hu Fangting	DATE	2025/9/10
			REV NO.	A