



RoHS Compliant

A
B
C
D
E





MEASURE POINT: QUADRANT POINT (QP) TANGENCY POINT (TP) INTERSECTION POINT (IP)		联晟欣连接器（深圳）有限公司 Lianshengxin Connector (Shenzhen) Co., Ltd			
UNLESS OTHERWISE SPECIFIED, TOLERANCE:		DESIGN	Andy	DATE	2014.12.24
X. ±0.25		CHECKED		DATE	
X.x ±0.20		APPROVED		DATE	
X.xx ±0.15		PART NO: LCK317BA0038A		REV: 04	SCALE: 1:1
ANGULAR ±3°		DRAWING NO: 102022802		UNIT: mm	
		TITLE: 充电弹片 L2.77×W1.34×H3.17 Shielding Clip, SMT		SHEET: 1/1	


1 2 3 4 5 6 7

RoHS Compliant

耳机插入示意图



RECOMMENDED PCB LAYOUT
TOLERANCE ± 0.05 (焊盘推荐图)
(FOR REFERENCE ONLY)




3D VIEW

NOTES:

- 1) MATERIAL:
1-1: STAINLESS STEEL THICKNESS $= 0.08 \pm 0.03 \text{ mm}$
- 2) FINISH:
2-1: $10 \mu\text{m}$ min Au PLATING ON CONTACT AREA,
 $1 \mu\text{m}$ min Au PLATING ON SOLDER AREA,
 $50 \sim 150 \mu\text{m}$ NICKEL UNDER PLATING OVER ALL.
- 3) PRODUCT SPECIFICATIONS:
3-1: RATED CURRENT: 1.5 A/MAX
3-2: VOLTAGE RATING: 5.0 V/AC/DC/MAX
3-3: CONTACT RESISTANCE: $50 \text{ m}\Omega/\text{MAX}$
3-4: DURABILITY: $10,000 \text{ CYCLES}$.
- 4) SALT SPRAY: 24 HOURS (JUDGED BY ALL OUTSIDE AREA)
- 5) DIMENSIONS MARKED $\square$, CPK > 1.33
- 6) ALL DIMENSIONS MARKED $\blacktriangledown$ MUST BE CONTROLLED BY QC;
- 7) COMPLIANT TO RoHS & LEAD FREE

耳机插入力曲线图



MEASURE POINT: QUADRANT POINT TANGENCY POINT INTERSECTION POINT		联晟欣连接器（深圳）有限公司 Lionshengxin Connector (Shenzhen) Co., Ltd			
UNLESS OTHERWISE SPECIFIED, TOLERANCE:		DESIGN	Andy	DATE	2014.12.24
X. ± 0.25		CHECKED		DATE	
X.x ± 0.20		APPROVED		DATE	
X.xx ± 0.15		PART NO: LCK317BA0038A		REV: 04	
ANGULAR $\pm 3^\circ$		DRAWING NO: 102022802		SCALE: 1:1	
				SHEET: 1/1	
				UNIT: mm	