


RoHS Compliant


REV.	ZONE	DESCRIPTION	DESIGN	DATE
B		NEW		







SECTION B-B
SCALE 1:1









SECTION A-A
SCALE 1:1

NOTE:

1.MATERIAL SPECIFICATION:
  1.HOUSING: HIGH TEMPERATURE RESISTANT PLASTIC,UL94 V-0.
  2.CONTACTS: COPPER ALLOY
  3.MID PLATE: STAINLESS STEEL
2.PLATING SPECIFICATION:
  2-1.CONTACTS:
    Ni 50u" MIN. UNDER PLATED OVER ALL.
    Au PLATED ON THE FUNCTIONAL AREA OF CONTACT.
    (GOLD PLATING THICKNESS FOLLOW THE P/N)
    GOLD FLASH PLATING ON SOLDER AREA
  2-2.FRONT SHELL:
    Ni 30u" MIN. UNDER PLATED OVER ALL.
3.MECHANICAL PERFORMANCE,
  3-1.INSERTION FORCE: 0.5~2.0kgf.
  3-2.REMOVAL FORCE: 0.8kgf~2.0kgf.
  3-3.DURABILITY: 10000 CYCLES.
4.ELECTRICAL PERFORMANCE,
  4-1. CURRENT RATING: 5A
       VOLTAGE RATING: 20V
  4-2.INSULATION RESISTANCE: 100MΩ MIN
  4-3.DIELECTRIC WITHSTAND VOLTAGE,AC 100V FOR 1 MINUTE.
  4-4.LOW CONTACT RESISTANCE: INITIAL 40MΩ
                              AFTER 50MΩ
5. ENVIRONMENTAL PERFORMANCE:
  OPERATING TEMPERATURE: -30°C~+80°C.
6.IR REFLOW:
  THE PEAK TEMPERATURE ON THE BOARD SHALL
  BE MAINTAINED FOR 10 SECONDS AT 260°C.

X. ±0.50	X.° ± 2°	UNITS	mm
.X ±0.30	.X° ± 1°		
.XX ±0.10	.XX° ± 0.5°	MAT'L	
.XXX ± 0.05			
		FINISH	
		Q'TY	

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD

深圳市创粤科技有限公司

TITLE:
TYPE-C 16PIN板上垫高1.0MM母座 四脚插板SMT CH=2.67MM

TYPE-C-16P-CH2.67L7.35-04003

DWG NO.:


CHKD:


DR:


SCALE	SHEET	REV.
1/1	1/1	A1

RoHS Compliant

REV.	ZONE	DESCRIPTION	DESIGN	DATE
B		NEW		







RECOMMEND P.C.B LAYOUT(COMPONENT SIDE)

TOLERANCE FOR PCB LAYOUT IS ± 0.05

USB TYPE-C PIN ASSIGNMENTS

PIN NUMBER	SIGNAL NAME
A1	GND
A4	VBUS
A5	CC1
A6	Dp1
A7	Dn1
A8	SBU1
A9	VBUS
A12	GND

PIN NUMBER	SIGNAL NAME
B12	GND
B9	VBUS
B8	SBU2
B7	Dn2
B6	Dp2
B5	CC2
B4	VBUS
B1	GND


X. ±0.50	X.° ± 2°	UNITS mm	深圳市创粤科技有限公司
.X ±0.30	.X° ± 1°		
.XX ±0.10	.XX° ± 0.5°	MAT'L	TITLE: TYPE-C 16PIN板上垫高1.0MM母座 四脚插板SMT CH=2.67MM
.XXX ± 0.05			
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD		FINISH	TYPE-C-16P-CH2.67L7.35-04003 / DWG NO.:
		Q'TY	CHKD:
			DR:


SCALE	SHEET	REV.
1/1	1/1	A1

REV.	ZONE	DESCRIPTION	DESIGN	DATE
B		NEW		

RoHS Compliant

出料方向
PULL OUT DIRECTEON







NOTES

1. 帶子引導長度
LEAD TAPE LENGTH
出料方向
PULL OUT DIRECTEON

出料方向
PULL OUT DIRECTEON



2. 上帶 剝力力為：0.1~1.3**N(10.2gf~130gf)**
PEELING OFF FORCE OF TOP TAPE:0.1~1.3N(10.2gf~130gf)
出貨'運輸過程中一定注意：
THIS REQUIREMENT SHOULD BE APPLIED AT SHIPMENT：
卷帶在運輸過程中不能散開
PEELING OFF SHOULD NOT BE ALLOWED DURING TRANSPORTATION



包裝明細表 (The detail of the packing) Carton

產品料號 (Product No.)	包裝容量 (Packing Capacity)			重量 Weight (Kg)		
	pcs/box	boxs/Carton	Pcs/Box	N.W./Pcs	N.W./Box	G.W./Box
	1000	14	14000	----	----	----

X. ±0.50	X.° ± 2°	UNITS mm	深圳市创粤科技有限公司
.X ±0.30	.X° ± 1°		
.XX ±0.10	.XX° ± 0.5°	MAT'L	TITLE: TYPE-C 16PIN板上垫高1.0MM母座 四脚插板SMT CH=2.67MM
.XXX ± 0.05			
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD		FINISH	TYPE-C-16P-CH2.67L7.35-04003 / DWG NO.:
		Q'TY	CHKD:
			DR:

SCALE	SHEET	REV.
1/1	1/1	A1