




RoHS

REV	ECN NO.	DESCRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	更换图框			2024.05.24

SPECIFICATIONS

1. Rated current: 5A AC, DC
2. Rating voltage: 250V AC DC
3. Temperature range: -40°C ~ +105°C
4. Insulation resistance: 1000MΩ Min.
5. Withstand voltage: 1500V AC/Minute
6. Contact resistance: 10mΩ Max.

Material:

Insulator :PA66 UL94V-0 Black

Contact :Brass

Plating: Tin plated over nickel

Circuits: 2-12

Mate with P3025 series Dual row housing

Ordering Code:

M3025V-2xXXP
1 2

1.序列号

2.Pin位数: 2x02P
2x12P

No.of PIN/ROW	Dimension	
	A	B
2x01	--	6.65
2x02	3.00	9.65
2x03	6.00	12.65
2x04	9.00	15.65
2x05	12.00	18.65
2x06	15.00	21.65
2x07	18.00	24.65
2x08	21.00	27.65
2x09	24.00	30.65
2x10	27.00	33.65
2x11	30.00	36.65
2x12	33.00	39.65

X.±0.50	X.°±	PART NO: M3025V-2xXXP	XFCN 兴飞连接器				
.X±0.25	.X°±						
.XX±0.15	.XX°±		TITLE: 3.00mm Crimp Style Connectors	0769-82001899			
.XXX±0.10	.XXX°±			www.xfconn.com			
UNITS:	mm	APPD Chen ZhiQiang		DWG NO: /			
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN							
				CHKD Liu Wei	VIEW		
				DRAW Chen HongJiang	SCALE	SHEET	REV
		DATE 2024.07.01	NONE	1/1	A1		