

Product Specification

XBLW LM285

Micropoer Voltage Reerence Diodes

WEB | www.xinboleic.com



Descriptions

The LM285 series are micropower two-terminal bandgap voltage regulator diodes. Designed to operate over a wide current range of 10uA to 20mA, these devices feature exceptionally low dynamic impedance, low noise and stable operation over time and temperature. Tight voltage tolerances are achieved by on-chip trimming. The large dynamic operating range enables these devices to be used in applications with widely varying supplies with excellent regulation. Extremely low operating current make these devices ideal for micropower circuitry like portable instrumentation, regulators and other analog circuitry where extended battery life is required.

The LM285series are packaged in SOP-8, SOT23-3L and TO-92 plastic case and areavailable in versions of 1.24V、2.5V.

Features


- Operating Current from 10uA to 20mA
- 1% Initial Tolerance
- Low Temperature Coefficient
- 0.6Ω Dynamic Impedance
- Low Voltage Reference 1.24V

Applications


- Instrumentation
- Process Control
- Energy Management
- Data Acquisition Systems
- Battery-Powered Equipment
- Precision Audio Components



TO-92



SOP-8



SOT-23-3L

Ordering Information


Product Model	Package Type	Marking	Packing	Packing Qty
XBLW LM285Z-1.2	TO-92	LM285Z1.2	Bag	2000Pcs/Bag
XBLW LM285M3X-1.2	SOT23-3L	28512	Tape	3000Pcs/Reel
XBLW LM285MX-1.2	SOP-8	LM285M1.2	Tape	2500Pcs/Reel
XBLW LM285Z-2.5	TO-92	LM285Z2.5	Bag	2000Pcs/Bag
XBLW LM285M3X-2.5	SOT23-3L	28525	Tape	3000Pcs/Reel
XBLW LM285MX-2.5	SOP-8	LM285M2.5	Tape	2500Pcs/Reel

Pin Configurations




TO-92

LM285Z-xx



SOT23-3L

LM285M3X-xx



SOP-8

LM285MX-xx

Pin Description

Pin Number			Symbol	Characteristics
TO-92*	SOT-23-3L	SOP-8		
2	1	8	+	Cathode
1	2	4	-	Anode
3	3	1,2,3,5,6,7	NC	No internal connections

*Note: XBLW LM285Z-1.2 and LM285Z-2.5 adopt a unique TO-92 package pin position definition, where the Pin-3 is NC. If the customer designs and applies the Pin-1 is NC and can be used by rotating the direction.

Function Block




Figure1 Function Block Diagram of LM285

Absolute Maximum Ratings

(TA = 25°C, unless otherwise noted)

Characteristics	Symbol	Value	Unit
Reverse Current	IR	30	mA
Forward Current	IF	10	mA
Operating Ambient Temperature Range	TA	-40 to +85	°C
Operating Junction Temperature	TJ	+150	°C
Storage Temperature Range	Tstg	-65 ~ +150	°C
Electrostatic Discharge Sensitivity (ESD) Human Body Model (HBM) Machine Model (MM) Charged Device Model (CDM)	ESD	4000 400 2000	V

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.


Electrical Characteristics

(TA = 25°C, unless otherwise noted)


Characteristics	Symbol	Test Conditions	Min	Typ	Max	Unit
Reverse Breakdown Voltage LM285-1.2 LM285-2.5	V(BR)R	IRmin ≤ IR ≤ 20mA	1.220 2.475	1.240 2.500	1.250 2.525	V
Reverse Breakdown Voltage LM285-1.2 LM285-2.5		IRmin ≤ IR ≤ 20mA -40°C to +85°C	1.210 2.450		1.260 2.550	V
Minimum Operating Current	IRmin			6	10	μA
		-40°C to +85°C			20	μA
Reverse Breakdown Voltage Change with Current	ΔV(BR)R	IRmin ≤ IR ≤ 1mA			1.5	mV
		-40°C to +85°C			5	mV
		1mA ≤ IR ≤ 20mA		4	10	mV
		-40°C to +85°C			20	mV
Reverse Dynamic Impedance	Z	IR = 100μA		0.6		Ω
Average Temperature Coefficient	ΔV(BR)/ΔT	10μA ≤ IR ≤ 20 mA -40°C to +85°C		80		ppm/°C
Wideband Noise (RMS)	n	IR = 100μA, 10Hz ≤ f ≤ 10 kHz		60		μV
Long Term Stability	S	IR = 100μA, TA = +25°C ± 0.1°C		20		ppm/kHR

Typical Application Circuit


Fixed Vref Type Circuit




Wide Input Range Reference




Reference from 1.5V Battery



Micropower Reference from 9V Battery



Micropower* 5V Regulator



Micropower* 10V Reference

Characteristics Curves

LM285-1. 2




Figure 2. Reverse Characteristics




Figure 3. Reverse Characteristics




Figure 4. Forward Characteristics




Figure 5. Temperature Drift




Figure 6. Noise Voltage




Figure 7. Response Time

LM285-2.5




Figure 8. Reverse Characteristics




Figure 9. Reverse Characteristics




Figure 10. Forward Characteristics




Figure 11. Temperature Drift




Figure 12. Noise Voltage





Figure 13. Response Time


Package Information

· T0-92

Symbol	Dimensions In Millimeters		Symbol	Dimensions In Inches	
	Min(mm)	Max(mm)		Min(in)	Max(in)
A	3.300	3.700	A	0.130	0.146
A1	1.100	1.400	A1	0.043	0.055
b	0.380	0.550	b	0.015	0.022
c	0.360	0.510	c	0.014	0.020
D	4.300	4.700	D	0.169	0.185
D1	3.430		D1	0.135	
E	4.300	4.700	E	0.169	0.185
e	1.270 (TYP)		e	0.050 (TYP)	
e1	2.440	2.640	e1	0.096	0.104
L	14.10	14.50	L	0.555	0.571
Φ		1.600	Φ		0.063
h	0.000	0.380	h	0.000	0.015





• SOT23-3L




COMMON DIMENSIONS
(UNITS OF MEASURE=MILLIMETER)

SYMBOL	MIN	NOM	MAX
A	-	-	1.25
*A1	0.01	-	0.08
A2	1.00	1.10	1.20
A3	0.60	0.65	0.70
b	0.33	-	0.41
c	0.11	-	0.20
D	2.82	2.92	3.02
*E	2.60	2.80	3.00
*E1	1.50	1.60	1.70
*e	0.90	0.95	1.00
e1	1.90BSC		
L	0.30	-	0.60
*L1	0.55	0.60	0.75
θ	0°	-	8°



• SOP-8

Size Symbol	Dimensions In Millimeters		Size Symbol	Dimensions In Inches	
	Min (mm)	Max (mm)		Min (in)	Max (in)
A	1.350	1.750	A	0.053	0.069
A1	0.100	0.250	A1	0.004	0.010
A2	1.350	1.550	A2	0.053	0.061
b	0.330	0.510	b	0.013	0.020
c	0.170	0.250	c	0.006	0.010
D	4.700	5.100	D	0.185	0.200
E	3.800	4.000	E	0.150	0.157
E1	5.800	6.200	E1	0.228	0.224
e	1.270 (BSC)		e	0.050 (BSC)	
L	0.400	1.270	L	0.016	0.050
θ	0°	8°	θ	0°	8°



Statement:

- XBLW reserves the right to modify the product manual without prior notice! Before placing an order, customers need to confirm whether the obtained information is the latest version and verify the completeness of the relevant information.
- Any semiconductor product may malfunction under specified conditions. When using XBLW products for system design and overall manufacturing, the buyer is responsible for complying with safety standards and taking appropriate safety measures to avoid risks that may cause personal injury or property damage.
- XBLW products have not been licensed for life support, military, and aerospace applications, and therefore XBLW is not responsible for any consequences arising from the use of this product in these areas.
- If any or all XBLW products (including technical data, services) described or contained in this document are subject to any applicable local export control laws and regulations, they may not be exported without an export license from the relevant authorities in accordance with such laws.
- The specifications of any and all XBLW products described or contained in this document specify the performance, characteristics, and functionality of said products in their standalone state, but do not guarantee the performance, characteristics, and functionality of said products installed in Customer's products or equipment. In order to verify symptoms and conditions that cannot be evaluated in a standalone device, the Customer should ultimately evaluate and test the device installed in the Customer's product device.
- XBLW documentation is only allowed to be copied without any alteration of the content and with the relevant authorization. XBLW assumes no responsibility or liability for altered documents.
- XBLW is committed to becoming the preferred semiconductor brand for customers, and XBLW will strive to provide customers with better performance and better quality products.

Specification information

Version	Release Date	New/Revised Content
V1.0	2024/10	Initial Writing
V2.0	2025/05	Update Template
V2.1	2026/09	Update foot position instructions