





REV.	DESCRIPTION OF REVISIONS	APPR.	CHKD.	DRAW.	DATE
△	Original reversion	lucky	lucky	Roy	2024/07/05



- NOTE:
- MECHANICAL:
 - MATING FORCE: 0.5~2.0Kgf
 - UMMATING FORCE: Initial: 0.8~2.0Kgf
After 500 to 10,000cycles: 0.6~2.0Kgf
 - FREQUENCY: 500±50 CYCLES/HOUR, 10000 CYCLES;
 - ELECTRICAL CHARACTERISTICS:
 - CURRENT RATING:

VBUS Pins (A4,A9,B4,B9): 5A Max;
1.25 Amps MAX. for Vconn (B5) with return path through the corresponding GND pins(Pin A1, A12, B1, B12).
Other All Pins 0.25A/Pin
 - INITIAL CONTACT RESISTANCE: 40mΩ Max.
 - INSULATION RESISTANCE: 100MΩ MIN
 - WITHSTANDING VOLTAGE: 100V AC, 1 MINUTE;
 - ENVIRONMENTAL
TEMPERATURE RANGE: -40°C TO +85°C.
 - Recommended thickness of steel mesh T=0.12mm.



ITEM	PART NAME	Q'TY	MATERIAL	FINISH
1	Molding	1	THERMOPLASTIC	Black, UL94V-0
2	CONTACT	24	HIGH CONDUCTIVITY COPPER	Contact area: Au 3u"
3	SHELL	1	STAINLESS STEEL	Ni plated over all
4	MID-PLATE	1	STAINLESS STEEL	Ni plated over all


Unless otherwise specified, other tolerance are:		MUP MUP INDUSTRIAL CO.,LTD.	
X	±0.40	X*	±5°
X.X	±0.30	X.X*	±4°
X.XX	±0.20	X.XX*	±3°
X.XXX	±0.10	X.XXX*	±2°

PROJ.	UNIT	SCALE	NAME: USB Type C Dual-Row SMT Receptacle	
⊕	mm	1:1	MODEL NO: MUP-U20201-31	
CUSTOMER DRAWING			TYPE: 24P & USB 3.2 Without GND-PLATE	
DRAW	Roy	2024/07/05	DWG NO.:	
CHECKED	lucky	2024/07/05	DWG-U20201-31-01	
APPROVAL	lucky	2024/07/05	SHEET	REVISION
			1/2	1

REV.	DESCRIPTION OF REVISIONS	APPR.	CHKD.	DRAW.	DATE
△	Original reversion	lucky	lucky	Roy	2024/07/05

NOTES

1. NUMBER OF CONNECTORS:900PCS/REEL
2. LEAD TAPE LENGTH




3. QUANTITY:9000/CARTON

4. WEIGHT :

4.1 NET WEIGHT : 4.9 Kg

4.2 GROSS WEIGHT : 8.9 Kg

5.Meas:350Lx350Wx315H mm



Unless otherwise specified, other tolerance are:			MUP MUP INDUSTRIAL CO.,LTD.			
X	±0.40	X*	±5*	NAME: USB Type C Dual-Row SMT Receptacle		
X.X	±0.30	X.X*	±4*	MODEL NO: MUP-U20201-31		
X.XX	±0.20	X.XX*	±3*	TYPE : 24P & USB 3.2 Without GND-PLATE		
X.XXX	±0.10	X.XXX*	±2*	DRAW	Roy	2024/07/05
PROJ.	UNIT	SCALE	DWG NO.:	CHECKED	lucky	2024/07/05
APPROVAL	lucky	2024/07/05	SHEET	REVISION	2/2	1
CUSTOMER DRAWING						