



Product Dimensions:




Electrical Schematic:



Electrical Characteristics

ITEM	SPECIFICATION	TEST CONDITION
INDUCTANCE	150-450uH	100KHz 0.1V (-40°C ~ +125°C)
LEAKAGE INDUCTANCE	4.5uH Max	100KHz 0.1V
DC RESISTANCE	TRANSFORMER SIDE=0.45Ω Max	AT 25°C
	CM CHOKE SIDE=0.8Ω Max	
TURNS RATIO	1CT:1CT±2%	100KHz 0.1V
INSERTION LOSS	-1.2 dB Max	4MHz
RETURN LOSS	-6 dB Min	4MHz
CMRR	-50 dB Typ	1-100MHz
HI-POT	6400VDC	1mA,60S
WORKING VOLTAGE	1500VDC	
CREEPAGE DISTANCE	>15mm	
CLEARANCE DISTANCE	>14mm	
OPERATING TEMPERATURE	-40°C ~ +125°C	
STORAGE TEMPERATURE	-50°C ~ +125°C	

Packaging Specifications:



Package Quantity:
One REEL=200Pcs
One CARTON=600Pcs

REFLOW SOLDERING CURVE

