








SPECIFICATION:

1.MATERIAL:

HOUSING:LCP 30% G/F UL 94V-0

COLOR:BLACK

CONTACT:BRASS C2680R-H,T=0.25mm

PEG: BRASS C2680R-H,T=0.30mm

2.FINISH:

CONTACT:1u"~15u"GOLD/TIN PLATING

ON CONTACT AREA

100u". TIN PLATING ON SOLDERTAILS

50u".NICKEL UNDERPLATING OVER ALL

PEG:100u". TIN PLATING ON SOLDERTAILS

50u".NICKEL UNDERPLATING OVER ALL

3.SPECIFICATION:

RATING VOLTAGE:12V AC

RATING CURRENT:1.5AMP

CONTACT RESISTANCE:30mΩ MAX

INSULATION RESISTANCE:1000MΩ MIN AT500V DC

WITHSTANDING VOLTAGE:AC 500V FOR 1 MINUTE

MATING FORCE:4.59KGF MAX(45N MAX)

EXTRACTION FORCE:1.02KGF MIN(10N MIN)

DURABILITY:500CYCLES

TEMPERATURE RANGE:-20℃ TO +85℃

环保要求		产品必须符合ROHS要求			制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA			料号 PART NO.	BX-SATA-04-7PSTG		版本 REV.	A
3	Peg	Brass C2680		Tin/Ni Plated				X.±0.30	X.°±3°	审核 CHECK	EVA			品名 TITLE	SATA 7P公座A型全电开背 斜长2.05mm 鱼叉触指式		页次 SHEET	1/1
2	Terminal	Brass C2680		Gold/Tin Plated				.X±0.20	.X°±2°	核准 APPROVAL	JADE			客户料号 CUTM.NO.				
1	Housing	High Temp	Black	UL 94V-0				.XX±0.05	.XX°±0.5°					Bossie (博锡)				
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK						单位 UNITS	MM	比例 SCALE	1:1					
1		2		3		4		5		6		7		8		9		