







SPECIFICATION:

1.MATERIAL:

HOUSING: LCP UL 94V-0

COLOR:BLACK

CONTACT: PHOSPHOR BRONZE

C5191R-H,T=0.25mm

PEG:C2680R-H,T=0.50mm

2.FINISH:

CONTACT:1u"/3u"/5u"/15u" GOLDPLATING


ON CONTACT AREA

100u" TIN PLATING ON SOLDER TAILS

30u" NICKEL UNDERPLATING OVER ALL

PEG:100u" TIN PLATING ON SOLDER TAILS

30u" NICKEL UNDERPLATING OVER ALL



RECOMMENDED PCB LAYOUT
PCB TOLERANCE:±0.05

环境要求		产品必须符合ROHS要求			制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA		料号 PART NO.	BX-SATA-02-22PSZM	版本 REV.	A
3	Peg	Brass C2680R-H		Tin/Ni Plated				X.±0.30	X.*±5°	审核 CHECK	EVA		品名 TITLE	SATA 7+15P 等速 DIP 180° 高脚间距及加长型全长2.7	页次 SHEET	1/1
2	Terminal	Pho.Bronze C5191R-H		Gold/Tin Plated				.X±0.20	.X.*±3°	核准 APPROVAL	JADE		客户料号 CUTM.NO.			
1	Housing	High Temp	Black	UL 94V-0				.XX±0.10	.XX.*±2°		单位 UNITS	MM	比例 SCALE	1:1		
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK												