






SPECIFICATION:

1.MATERIAL:

HOUSING: LCP 30% G/F UL 94V-0
COLOR:BLACK
CONTACT: PHOSPHOR BRONZE C5191R-H,T=0.25mm
PEG: BRASS C2680R-H,T=0.30mm

2.FINISH:

CONTACT:1u"/3u"/5u"/15u" GOLD PLATING ON CONTACT AREA
100u" TIN PLATING ON SOLDER TAILS
30u" NICKEL UNDERPLATING OVER ALL
PEG:100u" TIN PLATING ON SOLDER TAILS
30u" NICKEL UNDERPLATING OVER ALL



环境要求		产品必须符合ROHS要求			制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA		料号 PART NO.	BX-SATA-05-22PXTM	版本 REV.	A
3	Peg	Brass C2680R		Tin/Ni Plated				X.±0.30	X.*±3°	审核 CHECK	EVA		品名 TITLE	SATA 7+15P 单排脚直立式180°(欧型款)	页次 SHEET	1/1
2	Terminal	Pho.Bronze C5191		Gold/Tin Plated				.X±0.20	.X*±2°	核准 APPROVAL	JADE		客户料号 CUTM.NO.			
1	Housing	High Temp	Black	UL 94V-0				.XX±0.05	.XX*±0.5°		单位 UNITS	MM	比例 SCALE	1:1		
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK												