















LASER WELDING AREA SOLDER SPOT 5PCS
MIN VERTICAL BINDING FORCE 100NMIN



(正位度以8.96为中心后测量)



CAP ASSEMBLY AND MOUTING CONDITION(REF.)



品质管控等级要求		
符号	等级	产品管控要求
▼	重点要求	巡检，定义检验频率
▽	特殊性要求	CPK>1.33
◎	全检要求	自动机检验

UNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS:		ANGLES:	
X	: ± 0.5	X	: $\pm 2^\circ$
X.X	: ± 0.30	X.X	: $\pm 1^\circ$
X.XX	: ± 0.20		
X.XXX	: ± 0.10		









深圳市精睿兴业科技有限公司
SHENZHEN KRCONN TECHNOLOGY CO., LTD

TITLE	Type.C 16PIN Vertical DIP+SMT CONN. RECPTACLE			
DWN	chenjun	PART NO. TCR68-61121605-05		
CHKD	chenjun	SCALE:1:1	UNIT: mm	
APVD	Kevin.d	SIZE: A4	SHEET:1 OF 3	REV: A
DRAW NO. C-DWG-TCR68-05			CUSTOMER COPY	



REV.	ECN NO OR DESCRIPTION	REVISED	DATE
A	PROPOSE ONLY	ERIC	2023.11.22

CONN. PART NO.	CONN. QTY./REEL	REEL QTY./CARTON	CONN. QTY./CARTON
TCR68-61121605-05	600	10	6000 PCS



UNLESS OTHERWISE SPECIFIED TOLERANCES		深圳市精睿兴业科技有限公司 SHENZHEN KRCONN TECHNOLOGY CO., LTD			
DECIMALS:	ANGLES:	TITLE	Type.C 16PIN Vertical DIP+SMT CONN. RECPTACLE		
X : ± 0.5	X : $\pm 2^{\circ}$	DWN	chenjun	PART NO. TCR68-61121605-05	
X.X : ± 0.30	X.X : $\pm 1^{\circ}$	CHKD	chenjun	SCALE:1:1	UNIT: mm
X.XX : ± 0.20		APVD	Kevin.d	SIZE: A4	SHEET:3 OF 3
X.XXX : ± 0.10		DRAW NO. C-DWG-TCR68-05		CUSTOMER COPY	