







ROHS



6PIN



APPLICABLE FPC/FFC
T=0.30^{+0.02}/_{-0.01}



Recommended PCB mounting pattern and metal mask dimensions
Recommended metal mask thickness: t=0.1

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

NOTE:

1. MATERIAL:

HOUSING: HIGH TEMPERATURE THERMOPLASTIC(UL94V-0), COLOR: NATURAL.

CONTACTS: COPPER ALLOY.

PEG: COPPER ALLOY.

ACTUATOR: HIGH TEMPERATURE THERMOPLASTIC(UL94-V0).

2. RATING:

OPERATING VOLTAGE: 50Vrms AC.

CURRENT RATING: 0.5A.

OPERATING TEMPERATURE: -55°C~+85°C.

OPERATING HUMIDITY RANGE: RELATIVE HUMIDITY 90% MAX.(NO CONDENSATION)

STORAGE TEMPERATURE RANGE: -10°C~+50°C.

STORAGE HUMIDITY RANGE: RELATIVE HUMIDITY 90% MAX.(NO CONDENSATION)

INSULATION RESISTANCE >500MΩ.

WITHSTAND VOLTAGE: 200V/1 MINUTE.

NO.	COMPONENTS	MATERIALS	COLOR/SPECIFICATION	QUANTITY
1	HOUSING	LCP	NATURAL UL94V-0	1 PCS
2	COVER	PA9T	BLACK UL94V-0	1 PCS
3	CONTACT	PHOSPHOR BRONZE	T=0.15mm PLATING	POSITIONS
4	STATOR	BRASS	T=0.15mm PLATING	2 PCS

CUSTOMER DRAWING		LAILAN 深圳市莱联电子有限公司			
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO., LTD			
CHECKED					
APPROVED					
TOLERANCES ARE		TITLE	FPC连接器L 0间距6PIN翻盖式双侧触点上下接	REV.	A
30-150	±0.35	PART NO.	LAIL-FPC-CDX01-6P1.0-W	UNITS	mm
10-30	±0.2				
5-10	±0.15				
0-5	±0.1	DWG. NO.		Projection	