

1

2

3

4

5

6

7

8

SAMZO

REAC/ROHS

REV	ECN NO	DESRPTION	DESIGN	APPROVAL	DATE
A1	NEW	Replace frame			2019.06.12

Technical Requirements

1. Frequency: 0~3 GHz

2. Impedance: 50 Ω

3. VSWR: ≤ 1.35

4. Operating Voltage: 500 V

5. Withstand Voltage: 1500 V

6. Insulation Resistance: ≥ 5000 MΩ

7. Contact Resistance: Inner conductor ≤ 1.5 mΩ

Outer conductor ≤ 1 mΩ

8. Insertion Loss: ≤ 0.3 dB

9. Unspecified tolerances shall be ±0.2

18,7

11

14,3

1/4-36UNS-2B

9,6

11

BNC-KJ-187-L0-0-S

Transfer mode转接:SMA

Surface treatment镀层:镀金

Pin position脚位:180° 转接头

Length体长:18.7mm

Product number编号:KJ大纹系

Product series系列:BNC同轴射频天线座

ITEM	DESCRIPTION	MATERIAL	QTY	FINSH/COLOR															
C	插孔	HPB59-1	1	-----															
B	绝缘体	聚四氟乙烯	1	-----															
A	主体	黄铜	1	镀金															
					DESIGN	WANGGUIFA	2018.06.12												
					CHECKED	ZHENGUILAN	2018.06.12												
					APPROVED	LILIANJIANG	2018.06.14												

FIRST VIEW

SCALE

1:1

UNIT

mm

SAMZO COMPONENTS

Electronic switch and connector manufacturer

The copyright belongs to samzo parts [China] Co., Ltd. please use the material after samzo parts agree to authorize. The final right of interpretation belongs to samzo parts. WWW.SANCNN.COM

TITLE: BNC (Q9) 母转SMA公转接头BNC/SMA-KJ大网纹

DWG NO: BNC187-P001

PART NO: BNC187-071400

MODEL NO: BNC-KJ-187-L0-0-S

NAME: BNC COAXIAL RF CONNECTOR

1

2

3

4

5

6

7

8