







This document is the property of Xinshengyue Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Xinshengyue Corporation without its prior concert&that no right is granted to disclose or to use any information in this document.

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN
A	ECN NO.	NEW DRAWING	2026.06.10	Janus



RECOMMENDED P.C.B LAYOUT(PCB THICKNESS: 1.6mm)
COMPONENT SIDE VIEW(TOLERANCE: ±0.05mm)

- Connect Material:
- 1.Housing: Thermoplastic, PBT,UL94V-0, Color: Black;
 - 2.Insert: Thermoplastic, PBT,UL 94V-0, Color: Black;
 - 3.Shield: Brass T=0.2mm, 20u" Min Nickel Overall Plated;
 - 4.Input Terminal: Brass T=0.35mm, 40u" Min Ni UnderPlated Overall,80u" Min Tin On Solder Area;
 - 5.RJ45 Terminal: Phosphor Bronze T=0.35mm, 40u" Min Ni UnderPlated Overall, 80u" Min Tin On Solder Area; Selective 6u" Gold Plated On Contact Area;

TOLERANCE	NAME(INTENDED USE) CUSTOMER DRAWING	XSUA® 深圳市新升跃精密电子有限公司 SHENZHEN XINSHENGYUE PRECISION ELECTRONICS CO., LTD			
X.X ±0.30	X.* ±10°	PART NO.	TITLE: RJ45 1X1 100M VERTICAL H=16.95 W/LED W/SHIELD		
.XX ±0.20	.X* ± 8°		DRAWG NO. C-102004		
.XXX ±0.10	.XX* ± 5°				
UNITS	mm	DESIGN: Arvin			
MATERILA		CHED:			
FINISH		APPD:			
			SCALE 1:1	SHEET 1/2	REV. A

ELECTRICAL SPECIFICATIONS@25°C UNLESS OTHERWISE NOTED:

- 1.Turn Ratio(+/-5%): 1CT:1CT
- 2.Inductance OCL: 350uH Min @100KHz/0.1V/ 8mA DC Bias
- 3.Insertion Loss:

-1.0dB Max 1-100MHz
- 4.Return Loss:

-18dB Min 1-30MHz

-14dB Min 30-60MHz

-12dB Min 60-80MHz

-10dB Min 80-100MHz
- 5.Cross talk:

-30dB Min 1-100MHz
- 6.Common Mode Rejection:

-30dB Min 1-100MHz
- 7.Hipot Test: (pcb side to cable side)



2250VDC 3S 1mA Max
- 8.Operating Temperature Range: -40°C ~ +85°C
- 9.Storage Temperature Range: -40°C ~ +85°C
- 10.Peak Wave Soldering Temperature Is 260°C Max,10 Secs Max.
- 11.RJ45 Meets IEEE 802.3 Standards.
- 12.RJ45 Cavities Conform To FCC Rules And Regulation

Part 68 Subpart F.
- 13.Packaging Information: Tray,120pcs/Tray, 1080pcs/Carton.
- 14.LED Specification:

Emitting Color	λd (nm)Typ	Vf@I _f =20mA	I _r @V _r =5V
GREEN	565nm	1.8-2.4V	10uA Max
YELLOW	585nm	1.8-2.4V	10uA Max

LED COLOR P/N TABLE

LED ITEM	Left	Right
0	Non	Non
1	Green	Yellow
2	Yellow	Green
3	Green/Yellow	Green/Yellow
4	Green/Orange	Green/Orange
5	Green	Green/Yellow
6	Green	Green/Orange



P/N: 102004-120421

02:RJ45

SERIES NO.1,2,3...

LED COLOR:SEE TABLE

CONTACT PLATED

4: 6u" Au

TAIL SOLDER PLATED

0: SN

PACKAGING:2:TRAY

MAGNETIC:1:10/100BASE-T

SERIES NUMBER

XX: 001~999

TOLERANCE	NAME(INTENDED USE) CUSTOMER DRAWING	XSUA® 深圳市新升跃精密电子有限公司 SHENZHEN XINSHENGYUE PRECISION ELECTRONICS CO., LTD			
X.X ±0.30 X.* ±10°	PART NO.	TITLE: RJ45 1X1 100M VERTICAL H=16.95 W/ LED W/SHIELD			
.XX ±0.20 .X.* ± 8°	DESIGN: Arvin	DRAWG NO. C-102004			
.XXX ±0.10 .XX.* ± 5°					
UNITS mm	CHED:		SCALE	SHEET	REV.
MATERILA	APPD:		1:1	2/2	A
FINISH					