


General Description




V_R	$R_{DS(on) MAX}$	I_D Max.
-20V	35.7mΩ@-4.5V	-5A
	46.2mΩ@-2.5V	




Features

- Trench FET Power MOSFET
- Load Switch for Portable Devices.
- DC/DC Converter.
- Moisture Sensitivity Level 3



Mechanical Data

- SOT-23 Small Outline Plastic Package.
- Epoxy UL: 94V-0.
- Mounting Position: Any.



Package Marking and Ordering Information

Product ID	Pack	Marking	Qty(PCS)
2305B	SOT-23	S5	3000

Absolute Maximum Ratings (Ta=25°C unless otherwise noted)

Parameter		Symbols	Rating	Units
Drain-Source Voltage		VDS	-20	V
Gate-Source Voltage		VGS	±12	V
Continuous Drain Current	TA=25°C	ID	-5	A
	TA=100°C		-3	
Pulsed Drain Current (Note1)		IDM	-20	
Power Dissipation		PD	1.25	W
Junction Temperature		Tj	150	°C
Storage Temperature		Tstg	-55-+150	°C
Thermal Resistance From Junction to Ambient (Note2)		RθJA	100	°C/W

Electrical Characteristics (Ta=25℃, unless otherwise noted)

Parameter	Symbol	Test Conditions	Min.	Typ.	Max.	Unit
Static						
Drain-Source Breakdown Voltage	V(BR)DSS	VGS=0V, ID=-250uA	-20			V
Gate-Threshold voltage	VGS (th)	VDS=VGS, ID=-250uA	-0.4	-0.65	-1	V
Gate-body Leakage	IGSS	VDS=0V, VGS=±12V			±100	nA
Zero Gate Voltage Drain current	IDSS	VDS=-20V, VGS=0V			-1	uA
Drain-Source On-Resistance (Note3)	RDS(ON)	VGS=-4.5V, ID=-3A		27.5	35.7	mΩ
		VGS=-2.5V, ID=-2A		35.5	46.2	
Drain to Source Diode Forward Voltage	VSD	IS=-3A, VGS=0V			-1.2	V
Dynamic						
Input capacitance	Ciss	VDS=-10V, VGS=0V, f=1MHz		597		pF
Output capacitance	Coss			97		
Reverse Transfer capacitance	Crss			83		
Total gate charge	Qg	VDS=-10V, VGS=0 to -4.5V, ID=-5A		15		nC
Gate-source charge	Qgs			1.8		
Gate-drain charge	Qgd			2.8		
Switching						
Turn-on Time	td(on)	VGS=-4.5V, VDD=-10V, ID=-5A, RGEN=6Ω		4.5		ns
Rise time	tr			9.2		
Turn-off Time	td(off)			18.7		
Fall time	tf			3.3		
Drain-source body diode characteristics						
Continuous source-drain diode current	IS				-5	A
Pulse diode forward current	ISM				-20	

Notes:

1. Repetitive Rating:Pulse Width Limited by Maximum Junction Temperature.
2. RθJA is measured with the device mounted on a 1inch² pad of 2oz copper FR4 PCB.
3. Pulse Test: Pulse Width ≤300us, Duty Cycle≤0.5%

Typical Characteristics

Figure 1: Output Characteristics




Figure 2: Typical Transfer Characteristics




Figure 3: On-resistance vs. Drain Current




Figure 4: Body Diode Characteristics




Figure 5: Gate Charge Characteristics




Figure 6: Capacitance Characteristics











Figure 7: Normalized Breakdown voltage vs. Junction Temperature

Figure 8: Normalized on Resistance vs. Junction Temperature

Figure 9: Maximum Safe Operating Area

Figure 10: Maximum Continuous Drain Current vs. Case Temperature

Figure 11: Normalized Maximum Transient Thermal Impedance

Figure 12: Peak Current Capacity



Package Information

Carrier Dimension(mm)




Dimensions are in millimeter

Pkg Type	A	B	C	d	E	F	P0	P	P1	10*P0	W
SOT-23	3.15	2.77	1.22	Ø1.50	1.75	3.50	4.00	4.00	2.00	40.00	8.00
(Tolerance)	±0.1	±0.1	±0.1	±0.1	±0.1	±0.1	±0.1	±0.1	±0.1	±0.2	±0.1



Reel Dimension(mm)




Reel Option	D	D1	D2	G	H	I	W1	W2
7"Dia	Φ178.00	54.40	13.00	R78.00	R25.60	R6.50	9.50	12.30
Tolerance	±2	±1	±1	±1	±1	±1	±1	±1

Package Specifications


Package	Reel Size	Reel DIA. (mm)	Q'TY/Reel (Kpcs)	Box Size (mm)	QTY/Box (Kpcs)	Carton Size (mm)	Q'TY/Carton (Kpcs)
SOT23	7'	178	3	210*208*203	45	440*400*230	180

Recommended Soldering Profile for Rectifier Diodes (Pb Free)

a) Wave Soldering Profile




b) Reflow Soldering Profile (Pb Free Application), refer to IPC/JEDEC J-STD-020



Preheat/Soak Temperature Min (T _{smin}) Temperature Max (T _{smax}) Time (t _s) from (T _{smin} to T _{smax})	50 °C 200 °C 60-120 seconds
Melting Point of Solder (Sn Ag Cu)	217°C
Ramp-up Rate to 217°C(Melting Point of Solder)	3°C/sec
Time at Temp.>217°C (Melting Point of Solder)	60~150 Sec
Peak Temperature	255±5°C
Time within 5°Cbelow Peak Temp.	20~40 Sec
Cooling Rate	6°C/sec (max)
Time from 25°C to Peak Temp.	8min (max)


c) Manual Soldering

When using an electric soldering iron for manual soldering, it is recommended that the temperature does not exceed 300°C and the soldering time is less than 10 seconds.

Package Mechanical Data


SYMBOL	DIMENSIONS	
	MIN.	MAX.
A	0.900	1.150
A1	0.000	0.100
A2	0.900	1.050
b	0.300	0.500
c	0.080	0.150
D	2.800	3.000
E	1.200	1.400
E1	2.250	2.550
e	0.950TYP	
e1	1.800	2.000
L	0.550REF	
L1	0.300	0.500
θ	0°	8°

Unit: mm

Suggested Pad Layout

Note:

1. Controlling dimension: In millimeters.
2. General tolerance: $\pm 0.05\text{mm}$.
3. The pad layout is for reference purposes only.

Disclaimer

The information presented in this document is for reference only. Yancheng **Xirun Semiconductor Co., Ltd** reserves the right to make changes without notice for the specification of the products displayed herein to improve reliability, function or design or otherwise.

The product listed herein is designed to be used with ordinary electronic equipment or devices, and not designed to be used with equipment or devices which require high level of reliability and the malfunction of which would directly endanger human life (such as medical instruments, transportation equipment, aerospace machinery, nuclear-reactor controllers, fuel controllers and other safety devices), **Xirun Semiconductor** or anyone on its behalf, assumes no responsibility or liability for any damages resulting from such improper use of sale.

This publication supersedes & replaces all information previously supplied. For additional information, please visit our website [http:// www.x-semi.cn](http://www.x-semi.cn) , or consult your nearest **Xirun Semiconductor's** sales office for further assistance.