

Features


- 350W peak pulse power (8/20 μ s)
- Ultra low capacitance: 1pF typical
- Ultra low leakage: nA level
- Operating voltage: 3.3V
- Low clamping voltage
- Protects one power line or data line
- Complies with following standards:
 - IEC 61000-4-2 (ESD) immunity test
 - Air discharge: ± 30 kV
 - Contact discharge: ± 30 kV
 - IEC61000-4-5 (Lightning) 21A (8/20 μ s)
- RoHS Compliant



SOD-323

Mechanical Characteristics

- Package: SOD-323
- Lead Finish: Matte Tin
- Case Material: "Green" Molding Compound.
- Terminal Connections: See Diagram Below
- Marking Information: See Below



Circuit diagram

Applications

- USB Ports
- Smart Phones
- Wireless Systems
- Ethernet 10/100/1000 Base T



CC = Device code
Marking (Top View)

Ordering Information

Part Number	Packaging	Reel Size
JEB03CX	3000/Tape & Reel	7 inch

Absolute Maximum Ratings ($T_A=25^{\circ}\text{C}$ unless otherwise specified)

Parameter	Symbol	Rating	Unit
Peak pulse power ($t_p = 8/20\mu\text{s}$)	P_{pk}	350	W
Peak pulse current ($t_p = 8/20\mu\text{s}$)	I_{PP}	21	A
ESD according to IEC61000-4-2 air discharge	V_{ESD}	± 30	kV
ESD according to IEC61000-4-2 contact discharge		± 30	
Junction temperature	T_J	125	$^{\circ}\text{C}$
Operation temperature	T_{OP}	-40~85	$^{\circ}\text{C}$
Lead temperature	T_L	260	$^{\circ}\text{C}$
Storage temperature	T_{STG}	-55~150	$^{\circ}\text{C}$


Electrical Characteristics ($T_A=25^{\circ}\text{C}$ unless otherwise specified)

Parameter	Symbol	Condition	Min.	Typ.	Max.	Unit
Reverse maximum working voltage	V_{RWM}				3.3	V
Reverse leakage current	I_R	$V_{RWM} = 3.3\text{V}$		10	200	nA
Reverse breakdown voltage	V_{BR}	$I_T = 1\text{mA}$	4			V
Clamping voltage ¹⁾	V_{CL}	$I_{PP} = 16\text{A}$, $t_p = 100\text{ns}$		12		V
Dynamic resistance ¹⁾	R_{DYN}			0.41		Ω
Clamping voltage ²⁾	V_{CL}	$V_{ESD} = 8\text{kV}$		12		V
Clamping voltage ³⁾	V_{CL}	$I_{PP} = 1\text{A}$, $t_p = 8/20\mu\text{s}$		6	7	V
		$I_{PP} = 21\text{A}$, $t_p = 8/20\mu\text{s}$		15	17	V
Junction capacitance	C_J	$V_R = 0\text{V}$, $f = 1\text{MHz}$		1		pF


Notes:

- 1) TLP parameter: $Z_0 = 50\Omega$, $t_p = 100\text{ns}$, $t_r = 0.2\text{ns}$, averaging window from 70ns to 90ns. R_{DYN} is calculated from 4A to 16A.
- 2) Contact discharge mode, according to IEC61000-4-2.
- 3) Non-repetitive current pulse, according to IEC61000-4-5.


Typical Performance Characteristics (TA=25°C unless otherwise Specified)




Junction Capacitance vs. Reverse Voltage




Peak Pulse Power vs. Pulse Time




Clamping Voltage vs. Peak Pulse Current (tp = 8/20μs)



TLP Measurement




8 X 20μs Pulse Waveform




ESD Clamping Voltage
8 kV Contact per IEC61000-4-2

SOD-323 Package Outline Drawing



	MILLIMETERS		
	MIN	NOM	MAX
A	0.800	--	1.100
A1	0.800	--	0.900
A2	0.000	--	0.100
b	0.250	--	0.400
c	0.080	--	0.177
D1	1.600	1.700	1.800
D	2.300	--	2.800
E	1.150	--	1.400
L	0.475REF		
L1	0.100	--	0.500
Θ	0°	--	8°

Suggested Land Pattern



Unit: mm