

Features

We declare that the material of product compliance with RoHS requirements and Halogen Free.

2 Unidirectional transil functions

Low leakage current: $I_R \max < 20 \mu A$ at VRM


300W peak pulse power(8/20 μs)

Transient protection for data lines as per

IEC61000-4-2(ESD) $\pm 30KV$ (air) $\pm 30KV$ (contact)

IEC61000-4-5(Lightning) see IPPM below

SOT-23



05C

Applications

Computers

Printers

Communication systems

Absolute Maximum Rating


Parameter	Symbol	Limits	Unit
Peak Pulse Power (tp = 8/20 μs)	PPP	300	W
Lead Solder Temperature – Maximum (10 Second Duration)	TL	260	°C
Storage Temperature Range	Tstg	-55 ~ +150	°C
Operating Temperature Range	Top	-40 ~ +125	°C
Maximum junction temperature	Tj	150	°C
Electrostatic discharge	ESD		kV
IEC61000-4-2 air discharge		± 30	
IEC61000-4-2 contact discharge		± 30	

Electrical Characteristics (TA=25°C unless otherwise specified)

DEVICE	VRWM (V)	IR (μA) @VRWM	VBR (V) @IT (Note 1)	IT (mA)	VC (V) @IPP=1A	VC (V) @IPP=5A	IPP(A) @tp=8/20μs	C (pF) f=1MHz
	Max.	Max.	Min.		Max.	Max.	Max.	Max.
SM05T1G	5	5	6	1	9.8	12.5	17	220

1. 8/20 waveform used.

Symbol	Parameter
VRM	Stand-off voltage
VBR	Breakdown voltage
VCL	Clamping voltage
IRM	Leakage current
IPPM	Peak pulse current



RATING AND CHARACTERISTIC CURVES




Fig1. Peak Pulse Power VS Pulse Time






Fig2. Pulse Waveform





Soldering parameters

Reflow Condition		Pb-Free assembly (see as below)
Pre Heat	-Temperature Min ($T_{s(min)}$)	+150°C
	-Temperature Max($T_{s(max)}$)	+200°C
	-Time (Min to Max) (ts)	60-180 secs.
Average ramp up rate (Liquid us Temp (T_L) to peak)		3°C/sec. Max
$T_{s(max)}$ to T_L - Ramp-up Rate		3°C/sec. Max
Reflow	-Temperature(T_L)(Liquid us)	+217°C
	-Temperature(t_L)	60-150 secs.
Peak Temp (T_P)		+260(+0/-5)°C
Time within 5°C of actual Peak Temp (t_P)		30 secs. Max
Ramp-down Rate		6°C/sec. Max
Time 25°C to Peak Temp (T_P)		8 min. Max
Do not exceed		+260°C



Package Dimensions & Suggested Pad Layout

SOT23




SOT-23 mechanical data

UNIT	A	C	D	E	H _E	e	M	L	L ₁	a
mm	max	1.1	0.15	1.4	3.0	2.6	0.5	1.95	0.55 (ref)	0.36 (ref)
	min	0.9	0.08	1.2	2.8	2.2	0.3	1.7		0.15
mil	max	43	6	55	118	102	20	77	22 (ref)	14 (ref)
	min	35	3	47	110	87	12	67		6

Dimensions	SOT23
Z	2.9
X	0.8
Y	0.9
C	2.0
E	1.35

Tape & reel specification

Tape	Symbol	Dimension (mm)
	P0	4.00±0.10
	P1	4.00±0.10
	P2	2.00±0.10
	D0	1.55±0.10
	D1	1.05±0.10
	E	1.55±0.10
	F	3.60±0.10
	W	8.00±0.10
	A0	3.80±0.20
	B0	3.25±0.20
	K0	1.45±0.10
	T	0.25±0.05
	D2	178.0±3.0
	D3	55Min.
	D4	R24.0±3.0
	G	R82.0±3.0
	I	13.0±2.0
	W1	11.0±3.0
7" Reel	Quantity: 3000PCS	